

Philips  
commercial TV

69 cm (27")  
real flat

27HT7210D



## Integrated Digital TV for entertainment

and interactive services

Sleek and elegant RealFlat™ styling and integrated ATSC/QAM tuner provides superb picture quality with full commercial features. SmartPlug™ interface provides seamless pay-per-view connectivity and the ability to upgrade to new technology.

### **Vivid, natural and razor sharp images**

- Real Flat picture tube technology brings you lifelike images

### **Interactive features**

- SmartPlug Xpress & Serial Xpress Control interfaces
- Future proof by software upgradability

### **Reduced installation Time**

- Wireless SmartLoader for fast cloning
- Total Program Control

**PHILIPS**  
sense and simplicity

# Specifications

## Picture/Display

- Aspect ratio: 4:3
- Color cabinet: Silver Frost
- Diagonal screen size: 29 inch / 72 cm
- Picture enhancement: Scavem, AutoPicture (5 modes), Black stretch, Tint, Active Control, Comb Filter, Contrast Plus, Sharpness Adjustment, Smart Picture
- Visible screen diagonal (inch): 27 inch
- Display screen type: Real Flat picture tube

## Sound

- Sound Enhancement: Auto Volume Leveller, AutoSound (4 modes), Incredible Surround
- Sound System: Incredible Surround, Stereo
- Output power (RMS): 2 x 5W

## Convenience

- Remote Control: DVD, TV
- Clock: On/Off event timer, Sleep Timer
- On-Screen Display languages: French, Spanish, English
- User convenience: Closed Captioning (analog), Closed captioning (digital), Menu Languages, Vchip and parental lock
- Ease of Installation: Auto Volume Leveler
- Screen Format Adjustments: 4:3, 4:3 expand, 16:9 compress

## Tuner/Reception/Transmission

- TV system: NTSC, ATSC
- Cable: Unscrambled Digital Cable -QAM
- Stereo System: BTSC
- Terrestrial: ATSC (8VSB)
- Video Playback: NTSC
- Aerial Input: 75 ohm F-type

## Connectivity

- AV 1: CVBS in, Component Video in
- AV 2: CVBS, S-Video Y/C
- Front / Side connections: CVBS in, Headphone out
- Audio Output - Digital: AC3 over S/PDIF (Optical)
- AV 3: Monitor Out
- Connectivity Enhancements: External Loudspeaker connector, RJ12 SmartPlug connector, SmartCard Expansion Slot
- Other connections: Antenna F-type

## Power

- Mains power: AC 90-140V, 60Hz

## Dimensions

- Box dimensions in inch (W x H x D): 32.8 x 28.35 x 23.27 inch
- Product weight (lb): 96.8
- Set dimensions in inch (W x H x D): 28.98 x 22.83 x 19.29 inch
- Weight incl. Packaging (lb): 107.8

# Highlights

## Real Flat picture tube

The flatter tube provides a wider viewing angle while minimizing reflections for the best picture possible.

## SmartPlug & Serial Xpress

The Smartplug interface permits OEM or 3rd party decoders and controllers to interface with the TV.

## Upgradable software


The upgradable software architecture ensures that the TV is future proof and compatible with new technologies and developments, securing your investment.

## Wireless SmartLoader

Provides the ability to copy easy and wireless all programming settings from one TV set into other TV sets in less than a minute. The feature ensures uniformity between TV sets and significantly reduces installation time and costs.

## Total Program Control

Locks in commercial customized settings and features with a master TV set-up, significantly reducing installation time. Ensures uniformity across displays and prevents guests from altering pre-set formats.



Issue date 2011-06-07

Version: 4.0.9

12 NC: 8670 000 23825  
UPC: 0 37849 96753 9

© 2011 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)