



Philips
commercial TV

69 cm (27")
real flat

27ST6210

Ideal for entertainment systems

and interactive services

Sleek and elegant RealFlat™ styling gives you digital picture quality with full commercial features. SmartCard™ interface provides seamless pay-per-view connectivity and the ability to upgrade to new technology.

Vivid, natural and razor sharp images

- Real Flat picture tube technology brings you lifelike images
- Active Control optimizes picture quality whatever the source

Interactive features

- SmartCard™ Expansion Slot
- SmartPlug Xpress & Serial Xpress Control interfaces

Reduced installation Time

- Wireless SmartLoader for fast cloning
- Total Program Control

PHILIPS

sense and simplicity

Specifications

Picture/Display

- Aspect ratio: 4:3
- Diagonal screen size: 27 inch / 72 cm
- Visible diagonal screen size: 68 cm
- Picture enhancement: Comb Filter Digital, AutoPicture (5 modes), Dynamic Noise Reduction, Tint
- Picture processing: 60Hz Analog

Sound

- Sound Enhancement: Auto Volume Leveller, Incredible Surround
- Sound System: Stereo
- Output power (RMS): 2 x 3W

Convenience

- Remote control type: RL9820BK
- Clock: Sleep Timer
- On-Screen Display languages: American, French, Spanish
- Ease of Installation: Cloning of TV settings, Advanced Hotel Mode, Wireless Smart Loading
- User convenience: Vchip and parental lock, Closed Captioning (analog)

Tuner/Reception/Transmission

- TV system: NTSC
- Tuner Display: PLL
- Aerial Input: 75 ohm F-type Antenna
- Number of Preset Channels: 181

Connectivity

- AV 1: CVI, YPbPr(1Fh), CVBS in
- AV 2: S-Video, CVBS
- AV 3: Monitor Out
- Other connections: Monitor out, CVBS, L/R (cinch)
- Front: CVBS in, Audio L/R in
- Connectivity Enhancements: External speaker:1/8" Jack, SmartCard Expansion Slot, RJ12 SmartPlug connector

Power

- Mains power: AC 90-150V, 50/60Hz
- Adaptor type: 13', 3-prong
- Power consumption: 74 W (avg) W

Loudspeakers

- Built-in speakers: 2

Accessories

- Optional accessories: Mounting brackets/ stands, Set up Remote RC2573GR, Clone box CLON99BK (wired), Wireless SmartLoader 22AV1120

Dimensions

- Carton dimensions (WxDxH) inch: 41.2"x33.1"x32.6"
- Product dimension (WxDxH) inch: 35"x27"x23"
- Weight incl. Packaging (lb): 110 lbs
- Product weight (lb): 99 lbs

Highlights

Real Flat picture tube

The flatter tube provides a wider viewing angle while minimizing reflections for the best picture possible.

SmartCard™ Expansion Slot

Permits OEM or 3rd party decoders and controllers to be installed inside the television for custom designed component integration. Eliminates the need for external set-top decoders, controllers, or data terminals. Integrates system for superior control applications. Allows expandability for future upgrades. Prepared for digital applications.

Active Control

Active Control ensure that noise and sharpness improvements are continuously made at a rate of 60 times per second. By continually adjusting picture setting over 3,000 times per minute, Active Control Plus ensures that the viewing experience is optimized.

SmartPlug & Serial Xpress

The Smartplug interface permits OEM or 3rd party decoders and controllers to interface with the TV.

Wireless SmartLoader

Provides the ability to copy easy and wireless all programming settings from one TV set into other TV sets in less then a minute. The feature ensures uniformity between TV sets and significantly reduces installation time and costs.

Total Program Control

Locks in commercial customized settings and features with a master TV set-up, significantly reducing installation time. Ensures uniformity across displays and prevents guests from altering pre-set formats.

