

Philips
Professional LED TV

28" EasySuite
LED
DVB-T2/T/C

28HFL3010T



Incredible functionality for your guests

With smart hotel info pages

With this energy efficient LED TV, you enjoy the benefits of a dedicated Hospitality TV. Allow your guests to buy premium content, inform them via hotel info pages and use the latest remote technology for effortless installation and control

Great viewing experience and guest comfort

- LED TV for images with incredible contrast
- Eco-friendly design & flame retardant housing
- Low power consumption

Advanced hotel features and future proof

- SmartInstall for easy remote installation and maintenance
- MyChoice compatibility for recurring revenues
- Serial Xpress Protocol Easy for interactive systems
- Full Hotel, Healthcare and Prison Modes
- Prevent unauthorized use by local control locking

Differentiating guest experience

- SmartInfo for branded, interactive hotel info pages
- Additional headphone connection for personal listening
- Nurse-call compatibility optimized for the Healthcare sector
- On-screen clock display for optimal guest convenience



PHILIPS

Highlights

LED TV


With LED backlight you can enjoy low power consumption and beautiful lines combined with high brightness, incredible contrast and vibrant colors.

MyChoice compatible



MyChoice offers a simple and low-cost way to offer your guests premium TV channels. At the same time it delivers an additional revenue stream which allows you to recover your initial TV investment.

SmartInstall



SmartInstall makes installation and maintenance of your TVs effortless. With a simple to use web tool, you can now remotely configure and install your TVs without visiting any rooms! This saves you time and makes sure your guests are not disturbed. Whether it is updating the hotel info pages or installing new channels, SmartInstall can handle all.

SmartInfo



SmartInfo allows you to provide hotel or city information to your guests. Your guests have access to this interactive hotel webpage even when the TV is not connected to your intranet or internet. You can change the information regularly and easily to keep your guests up to date with all the latest developments in your hotel.

SXP Easy



With Serial Xpress Protocol Easy the TV can be connected to external decoders and set-top boxes of all major interactive system providers.

Nurse-call compatibility

Nurse-call system compatibility makes Philips Healthcare TVs a highly integrated tool that provides not only entertainment options for the user/patient but also gives convenient access to help in medical emergencies.

On-screen clock display

With our new on-screen clock display, guests can easily access the current time. At a push of a button the clock is being displayed on the TV screen combining enhanced visibility and lower power consumption.

Local control locking

By disabling or enabling the local control locking, the administrator can prevent unauthorized use of the TV via the control buttons, saving the hotelier overheads.

Eco-friendly design

Sustainability is integral to the way Philips does business. Philips TVs are designed and produced according to our EcoDesign principles aimed at minimizing overall environmental impact, through lower power consumption, removal of hazardous substances, lower weight, more efficient packaging and better recyclability. Philips TVs also have a special housing of flame retardant material. Independent tests carried out by emergency fire services have shown that whereas TVs can sometimes intensify fires caused by external sources, Philips TVs will not contribute to the fire.

Low power consumption

Philips TVs are designed to minimize power consumption. This will not only reduce environmental impact but also lower operating costs.

Specifications

Picture/Display

- Display: LED HD TV
- Diagonal screen size: 28 inch / 70 cm
- Aspect ratio: 16:9
- Panel resolution: 1366 x 768p
- Brightness: 310 cd/m²
- Viewing angle: 178° (H) / 178° (V)
- Picture enhancement: Pixel Plus HD, 200Hz Perfect Motion Rate

Audio

- Sound output Power: 10 (2x5) W
- Speakers: 2.0, Down Firing
- Sound Features: AVL, Incredible surround, Dynamic Bass, Dolby MS10

Design

- Colour: Black

Tuner/Reception/Transmission

- Digital TV: DVB-T/T2/C
- Analog TV: PAL
- Video Playback: NTSC, PAL, SECAM

Connectivity Rear

- Antenna: IEC-75
- HDMI1: HDMI 1.4
- Digital Audio out: Optical
- Scart: RGB, CVBS, SVHS
- VGA input: 15 pin D-sub
- AV input: CVBS shared with YPbPr
- Component: YPbPr + L/R cinch
- DVI audio in: Mini-Jack
- External Control: RJ-48

Connectivity Side

- HDMI2: HDMI 1.4
- USB1: USB 2.0
- Common Interface Slot: CI+ 1.3
- Headphone out: Mini-Jack

Connectivity Enhancements

- HDMI: ARC (all ports), DVI (all ports)
- EasyLink (HDMI CEC): One touch play, System Standby, RC pass through, system audio control
- Scart: Power on scart
- RJ48: IR-In/Out, Serial Xpress interface

Features

- Digital services: 8d EPG, Now&Next, MHEG, Teletext, HbbTV
- Ease of use: Picture Style, Sound Style, Picture

Format

- Local control: On/Off switch (side)

Hospitality Features

- Hotel mode: Menu lock, Installation Menu Lock, Volume limitation, Local Control Lock
- Prison mode: high security mode, TXT/MHEG/USB/EPG/Subtitle Lock
- SmartInfo: HTML5 Browser, Interactive Templates, Picture Slide Show
- CMND Create & Control: Off-Line Channel Editor, Off-Line Settings Editor, Remote Management over RF, Content Creation
- Your brand: SmartInfo, Welcome Logo, Welcome Message, Customizable Dashboard (HTML)
- Revenue generation: MyChoice
- Cloning and Firmware update: Instant Initial Cloning, Via USB/RF
- Timer: Sleep Timer, Wake Up Alarm, Wake Up On Channel, Wake up Sounds
- Clock: Clock in Standby Mode, Glow-in-the-Dark RC button, On-screen Clock, Optional External Clock
- Channels: Combined List
- Interactive DRM: VSecure
- Control: Block Automatic Channel Update, Serial Xpress Protocol
- Power control: Auto Power ON, Green/fast startup
- Switch On control: Channel, Feature, Picture Format, Volume
- Remote Control: Cable Strap Ready, Low Battery Detection, RC Battery Door Lock
- Anti-Theft: Battery Anti-theft Protection, Kensington Lock

Healthcare features

- Control: Multi-Remote Control, Healthcare RC compatible, Nurse call system compatible
- Convenience: Headphone out, Independent main speaker mute
- Safety: Double isolation class II, Flame retardant

Multimedia

- Multimedia connections: USB
- Video playback supported: Formats: H.264/MPEG4 AVC, MPEG1, MPEG2, MPEG4, WMV9/VC1, Containers: AVI, MKV, 3GP, ASF, M2TS, M4V, MP4, MPG, PS, Quicktime, TS, WMV
- Subtitle formats supported: SRT, ASS, SMI, SSA SUB, TXT
- Music formats supported: MP3, AAC, WAV, WMA (v2 up to v9.2)

- Picture formats supported: BMP, JPG, PNG, GIF
- Supp. Video Resolution on USB: up to 1920x1080p@60Hz

Accessories


- Included: Remote Control 22AV1409A/12, Tabletop Stand, 2xAAA Batteries, Warranty Leaflet, Legal and Safety brochure, Power Cord
- Optional: External Clock 22AV1120C/00, Healthcare RC 22AV1109H/12, Setup RC 22AV9573A

Power

- Mains power: AC 220-240V; 50-60Hz
- Energy Label Class: A+
- Eu Energy Label power: 18 W
- Annual energy consumption: 26 kWh
- Standby power consumption: <0.3W
- Power Saving Features: Eco mode
- Ambient temperature: 0 °C to 40 °C

Dimensions

- Set dimensions (W x H x D): 635 x 393 x 62/74 mm
- Set dimensions with stand (W x H x D): 635 x 438 x 190 mm
- Product weight: 4.5 kg
- Product weight (+stand): 5.1 kg
- VESA wall mount compatible: M4, 100 x 100 mm



Issue date 2017-03-16

Version: 1.0.1

12 NC: 8670 001 25776
EAN: 87 18863 00398 5

© 2017 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* Availability of features will depend on implementation chosen by integrator.

* Typical on-mode power consumption measured according to IEC62087 Ed 2. The actual energy consumption will depend on how the television is used.

* This television contains lead only in certain parts or components where no technology alternatives exist in accordance with existing exemption clauses under the RoHS Directive.