



Philips  
Professional LCD TV

**32" EasySuite**  
LCD  
DVB-T MPEG 2/4

**32HFL3232D**

## Perfectly reliable to your guests

### Philips Hospitality LCD TV

With this modern and energy efficient Hospitality LCD TV, you will enjoy all the benefits of digital television. Your guests will enjoy a warm welcome and great viewing experience with this professional hotel TV.

#### **Advanced hotel features and future proof**

- Full HD LCD display, with a 1920x1080p resolution
- Integrated Connectivity Panel
- Installation menu locking
- Welcome message on screen display
- Programmable Switch On Channel
- One combined channel list for Analog and Digital channels

#### **Differentiating guest experience**

- Advanced EPG and channel list
- Volume limitation
- Additional headphone connection for personal listening
- Enjoy photo and music playback via USB

#### **Sustainable and safe**

- Low power consumption
- Eco-friendly design & flame retardant housing

# PHILIPS

# Highlights

## Full HD LCD display 1920x1080p



The Full HD screen has the widescreen resolution of 1920 x 1080p. This is the highest resolution of HD sources for the best possible picture quality. It is fully future proof as it supports 1080p signals from all sources, including the most recent like Blu-ray and advanced HD game consoles. The signal processing is extensively upgraded to support this much higher signal quality and resolution. It produces brilliant flicker-free progressive scan pictures with superb brightness and colors.

## Integrated Connectivity Panel

The Integrated Connectivity Panel allows your guests to seamlessly connect their personal

devices to your TV without the need of any external Connectivity Panel.


## Welcome message

A welcome greeting is displayed each time the TV set is switched on.

## Eco-friendly design

Sustainability is integral to the way Philips does business. Philips TVs are designed and produced according to our EcoDesign principles aimed at minimizing overall environmental impact, through lower power consumption, removal of hazardous substances, lower weight, more efficient packaging and better recyclability. Philips TVs also have a special housing of flame retardant material. Independent tests carried out by emergency fire services have shown that whereas TVs can sometimes intensify fires caused by external sources, Philips TVs will not contribute to the fire.

## USB for photo & music playback



The USB connector allows access to jpeg photos and mp3 music of most USB-sticks (USB memory-class device). Plug the USB into the slot at the side of the TV and access the multimedia content using the easy on screen content browser. You can now view and share your photos and music.

## Programmable Switch On Channel

Perfect for in-house advertising or information channels as it allows to show a predefined channel when the TV is turned on.

## Advanced EPG and channel list

The attractive EPG and channel list includes intuitive buttons with clear guiding graphics for easily finding your favorite channels.

## Hospitality features

All Philips Hospitality TVs are especially made for the hospitality, detention and healthcare environments. Special features include volume limitation, menu locking, cloning and a special remote control.



# Specifications

## Picture/Display

- Aspect ratio: Widescreen
- Brightness: 400 cd/m<sup>2</sup>
- Response time (typical): 5 ms
- Viewing angle: 178° (H) / 178° (V)
- Diagonal screen size: 32 inch / 81 cm
- Display screen type: LCD Full HD W-UXGA Act. matrix
- Panel resolution: 1920x1080p
- Picture enhancement: 3/2 - 2/2 motion pull down, 3D Combfilter, Active Control, Color Enhancement, Digital Crystal Clear, Digital Noise Reduction, Dynamic contrast enhancement, Sharpness Adjustment, 2D/3D noise reduction, 1080p 24/25/30Hz processing, 1080p 50/60Hz processing
- Screen enhancement: Anti-Reflection coated screen
- Dynamic screen contrast: 100,000:1
- Peak Luminance ratio: 74 %

## Supported Display Resolution

### Computer formats

Resolution	Refresh rate
640 x 480	60Hz
800 x 600	60Hz
1024 x 768	60Hz
1280 x 720	60Hz
1280 x 768	60Hz
1280 x 1024	60Hz
1360 x 768	60Hz

### Video formats

Resolution	Refresh rate
480i	60Hz
480p	60Hz
576i	50Hz
576p	50Hz
720p	50, 60Hz
1080i	50, 60Hz
1080p	24, 50, 60Hz
1080p	24, 25, 30, 50, 60Hz

## Sound

- Output power (RMS): 2 x 10W
- Sound Enhancement: Auto Volume Leveller, Incredible Surround, Smart Sound, Treble and Bass Control
- Sound System: Mono, Nicam Stereo, Stereo

## Convenience

- Clock: Sleep Timer
- Ease of Installation: Auto Program Naming, Automatic Channel Install(ACI), Automatic Tuning System (ATS), Autostore, Fine Tuning, PLL Digital Tuning, Plug & Play, Advanced Hotel Mode, Cloning of TV settings via USB, Installation menu locking, Keyboard lock-out, Security menu access
- Ease of Use: Auto Volume Leveller (AVL), On Screen Display, Side Control, 1 channel list analog/digital, Graphical User Interface, Program List
- Electronic Program Guide: 8 day Electronic Program Guide, Now + Next EPG
- Remote Control: TV, battery anti-theft protection, low battery detection
- Screen Format Adjustments: 4:3, Auto Format, Super Zoom, Movie expand 14:9, Movie expand 16:9, Subtitle Zoom, Widescreen
- Teletext: 1000 page Smart Text
- Comfort: Hotel Guest features, Sleep timer, Switch on channel, Volume limitation, Welcome message
- Firmware upgradeable: Firmware upgradeable via RF, Firmware upgradeable via USB
- Interactive hotel features: Block automatic channel update, Block over-the-air SW download
- Other convenience: Kensington lock
- Remote control type: 22AV1104B (RC6)
- Teletext enhancements: Fast text, Program information Line

## Multimedia Applications

- Multimedia connections: USB
- Playback Formats: MP3, Slideshow files (.alb), JPEG Still pictures

## Tuner/Reception/Transmission

- Aerial Input: 75 ohm coaxial (IEC75)
- TV system: PAL I, PAL B/G, PAL D/K, SECAM B/G, SECAM D/K, SECAM L/L', DVB COFDM 2K/8K
- Video Playback: NTSC, SECAM, PAL
- Digital TV: DVB-T MPEG4
- Tuner bands: Hyperband, S-Channel, UHF, VHF
- Number of Preset Channels: 999

## Connectivity

- Ext 1 Scart: Audio L/R, RGB
- Ext 2 Scart: Audio L/R, CVBS in
- Number of Scarts: 2

- Ext 3: YPbPr, Audio L/R in
- HDMI 1: HDMI v1.3
- Front / Side connections: HDMI v1.3, CVBS in, Audio L/R in, Headphone Out, USB 2.0
- Other connections: PC Audio in, PC-In VGA, S/PDIF out (coaxial), Common Interface
- EasyLink (HDMI-CEC): One touch play, System standby
- Number of HDMI connections: 2

## Power

- Ambient temperature: 5 °C to 35 °C
- Mains power: 220-240V; 50Hz
- Power consumption (typical): 105 W
- Standby power consumption: 0.23W
- Annual energy consumption: 123 kWh
- Mercury content: 42 mg
- Presence of lead: Yes\*

## Dimensions

- Set dimensions (W x H x D): 796 x 508.3 x 93 mm
- Set dimensions with stand (W x H x D): 796 x 556 x 220 mm
- Weight incl. Packaging: 12.8 kg
- Product weight: 8.3 kg
- Product weight (+stand): 9.4 kg
- Box dimensions (W x H x D): 1026 x 610 x 160 mm
- VESA wall mount compatible: 200 x 200 mm

## Accessories

- Included accessories: Table top stand, Power cord, Warranty Leaflet, Remote Control, Batteries for remote control
- Optional accessories: Set up remote 22AV8573/00, Wallmount (tilt) 22AV3200/10

## Green Specifications

- Low Power Standby
- Safety: Flame retardant housing
- SmartPower Eco


## Healthcare

- Convenience: Headphone out
- Safety: Double isolation Class II

## Loudspeakers

- Built-in speakers: 2

## Rear connectors



## Side



Issue date 2019-05-08

Version: 2.0.2

12 NC: 8670 000 69041  
EAN: 87 12581 56540 4

© 2019 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)