



Philips
Healthcare LCD TV

81cm/32"

LCD
Pro:Idiom™ with MPEG-4



32HFL5763H

The optimal Healthcare HD LCD TV

MPEG-4 and Pro:Idiom™ Plus

This HealthCare LCD TV delivers a superior picture with razor sharp images and brilliant colors. Designed for Hospital use, this set is enabled and complete with Pro:Idiom, SmartPort and IPTV connections.

Designed for Hospital Use

- Integrated pillow speaker interface
- UL Approved for hospital use
- XpressIO Port

Best Total Cost of Ownership

- Five Star Service - two-year advanced exchange warranty
- SmartPower² and ESP for energy saving

Sustainable and Safe

- Lead-free/RoHS compliant with flame retardant housing
- Eco-sensitive materials and packaging

Differentiating Guest Experience

- USB media autoplay

PHILIPS

Highlights

Five Star Service- warranty

Philips offers unmatched commitment to keeping your guest rooms in working order. Our products are so reliable that we offer a two-year advanced exchange warranty. In the event that something does go wrong, we guarantee to ship a replacement set to you, within 72 hours during the first year.

SmartPower² and ESP for energy

SmartPower² and ESP for energy saving

Lead-free/RoHS

In addition to being lead-free and RoHS compliant, Philips TVs have a special housing of eco-friendly, non-brominated flame-retardant materials. Independent tests carried out by emergency fire services have shown that

whereas TVs can sometimes intensify fires caused by external sources, Philips TVs will not contribute to the fire.

USB media autoplay

Philips TVs feature a USB connector that allows the guest to connect USB memory sticks to play music or photos right on the TV.

Specifications

Picture/Display

- Aspect ratio: Widescreen
- Panel resolution: 1366 x 768p
- Brightness: 380 cd/m²
- Contrast ratio (typical): 1100:1
- Response time (typical): 8 ms
- Diagonal screen size: 32 inch / 81 cm
- Visible screen diagonal (inch): 31.5 inch
- Picture enhancement: 3/2 - 2/2 motion pull down, 3D Combfilter, Digital Noise Reduction, Progressive scan, 1080p 24/25/30Hz processing, Automatic skin tone correction, Color Enhancement, Color Transient Improvement, Contrast Plus, Jagged Line Suppression, Motion adaptive de-interlacing, Active Control
- Display screen type: LCD WXGA Active Matrix TFT
- Visible diagonal screen size: 80.00 cm
- Screen enhancement: Anti-Reflection coated screen
- Viewing angle: 178° (H) / 178° (V)

Supported Display Resolution

Computer formats

Resolution	Refresh rate
640 x 480	60Hz
800 x 600	60Hz
1024 x 768	60Hz
1366 x 768	60Hz

Video formats

Resolution	Refresh rate
480i	60Hz
480p	60Hz
720p	60Hz
1080i	60Hz
1080p	24, 25, 30, 50, 60Hz

Sound

- Equalizer: 5-bands
- Output power (RMS): 2 x 10W
- Sound Enhancement: Auto Volume Leveller
- Sound System: Dolby Digital (AC-3), Stereo

Loudspeakers

- Built-in speakers: 2

Convenience

- Ease of Installation: PLL Digital Tuning, Program Name, Cloning of TV settings via USB, Cloning of

- TV settings via RF, Keyboard lock-out, Security menu access, Installation menu locking
- Ease of Use: Auto Volume Leveller (AVL), Smart Picture, Smart Sound
- Screen Format Adjustments: 4:3, 7 Widescreen Modes
- Comfort: Sleep timer, Switch on channel, Volume limitation, Welcome message
- User convenience: Closed captioning (digital), Vchip and parental lock
- Interactive features: Connectivity panel compatible
- SmartFeatures: SmartAudioSelect, SmartClone, SmartCP, SmartGuide Categories, SmartInstall, SmartLogo, SmartPower, SmartRC, SmartUpdate, SmartWindow, SmartSecure

Tuner/Reception/Transmission

- Tuner bands: Hyperband, UHF, VHF
- TV system: ATSC, NTSC
- Video Playback: NTSC
- Number of Preset Channels: 250
- Terrestrial: ATSC (8VSB)
- Aerial Input: 75 ohm F-type

Connectivity

- AV 1: CVBS in, Audio L/R in
- AV 2: YPbPr, Audio L/R in
- Front / Side connections: CVBS in, Audio L/R in, VGA PC-In, PC audio in 3.5 mm jack, HDMI, USB
- Other connections: Antenna F-type, RS232 Serial, S/PDIF out (coaxial), Analog audio Left/Right out, Ethernet
- Connectivity Enhancements: External Loudspeaker connector, SPI port
- HDMI 1: HDMI
- HDMI 2: HDMI
- HDMI 3: HDMI

Power

- Mains power: 120V - 60Hz
- Maximum Power Consumption: 110 W
- Standby power consumption: < 1 W
- Ambient temperature: 0 °C to 40 °C

Dimensions

- Set dimensions in inch (W x H x D): 30.65 x 20.25 x 4.13 inch
- Product weight (lb): 20.28
- Weight incl. Packaging (lb): 24.47

- VESA wall mount compatible: 200 x 200 mm
- Box dimensions in inch (W x H x D): 37.60 x 24.37 x 6.85 inch

Accessories

- Included accessories: Warranty Leaflet, Quick start guide, 3.5mm to 6.3mm jack cable, Power cord (1.8m)
- Optional accessories: Set up Remote RC2573GR, Mounting brackets/ stands, Guest remote control, Table top Stand with Swivel

Multimedia Applications

- Multimedia connections: USB
- Playback Formats: JPEG Still pictures, MP3, Slideshow files (.alb), Flash(*.swf, flv container)

Green Specifications

- Safety: Flame retardant housing
- Eco Designed
- Low Power Standby
- SmartPower Ultra

Healthcare

- Control: Multi remote control, Pendant control connector
- Convenience: Independent main speaker mute
- Safety: Galvanic isolated connections, Grounded power cord



Issue date 2014-03-14

Version: 3.1.7

12 NC: 8670 000 87184
UPC: 6 09585 22329 5

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* Five Star Advanced Exchange warranty is valid in the United States only. Local warranties govern sales in other countries.