

# PHILIPS

Xenon car headlight bulb

Xenon Vision

Type of lamp: D3R

Pack of: 1

42 V,35 W



42306VIC1



## Feel safe, drive safe

### Ideal for replacement

Philips Xenon Vision replaces a single burned-out lamp while matching the color of the unchanged one thanks to its new single-lamp replacement technology. Therefore it is the ideal replacement lamp and it's economical too!

#### **The reference in case of xenon lamp replacement**

- Replace one by one
- Xenon Vision perfectly matches the unchanged Xenon lamp

#### **Xenon quality and ultra resistant car lamp**

- Philips is the inventor of Xenon HID technology
- Philips car lamps are highly UV resistant
- Philips car lamps are made of high-quality quartz glass
- Philips car lamps are highly resistant against humidity

#### **Original Equipment manufacturer**

- Philips is the choice of major car manufacturers
- Award winning car lamp manufacturer
- Respecting high quality standards of the ECE homologation

# Highlights

## Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

## ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

## Rewarded Car lamps



Our lamps are often rewarded by automotive experts

## Economical choice

Thanks to its single lamp replacement technology Xenon Vision allows you to change your bulbs one by one while matching the color temperature of the unchanged lamp. It is the most economical choice for lamp replacement.

## Original Xenon technology



Xenon HID (High Intensity Discharge) lamps offer twice as much light for safer driving in all conditions. As a matter of fact, the intense white light produced by the Xenon HID lamps is comparable to daylight. Studies have demonstrated that xenon automotive lighting helps drivers to concentrate on the road and to distinguish obstacles and road signs much faster than traditional lamps.

## Single-lamp replacement

Philips Xenon Vision replaces a single burned-out lamp while matching the color of the unchanged one. Its new single-lamp replacement technology allows for one-by-one replacement while still matching the color temperature of the unchanged lamp. Thus, Xenon Vision is the perfect solution for single-lamp replacement.

## UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensures their longevity

## High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light.

## Resistance against humidity

Only a burning bulb made of quartz glass can resist thermal shocks : if a drop of cold water touches the hot bulb, which can happen when you drive through water with a broken headlight unit.

# Specifications

## Packaging Data

EAN3: 8727900364842  
EAN1: 8727900364835  
Packaging type: C1

## Electrical characteristics

Voltage: 42 V  
Wattage: 35 W

## Lifetime

Life time: Up to 2500h

## Light characteristics

Lumens: 2800 ±450 lm  
Color temperature: Up to 4300 K

## Ordering information

Order entry: 42306VIC1  
Ordering code: 36483533

## Outerpack information

Height: 5.7 cm  
Length: 11.1 cm  
Width: 9.6 cm  
Gross weight per piece: 0.203 kg

## Product description

Type: D3R  
Application: High beam, Low beam  
Designation: D3R Vision  
Homologation ECE  
Marking ECE: E4 OBO

Range: Xenon Vision

Technology: Xenon

Base: PK32d-6

## Packed product information

Pack Quantity: 1  
MOQ (for professionals): 2  
Gross weight per piece: 97 g  
Height: 9.3 cm  
Length: 5.4 cm  
Net weight per piece: 73.2 g  
Width: 5.4 cm

## Marketing specifications

Expected benefits: More light  
Product highlight: Ideal for replacement

