



Philips Vision
Xenon car headlight bulb

Type of lamp: D4S

Pack of: 1
42 V, 35 W



42402VIC1

Feel safe, drive safe

Feel safe, drive safe

Philips Xenon Vision replaces a single burned-out lamp while matching the colour of the unchanged one thanks to its new single-lamp replacement technology. Therefore it is the ideal replacement lamp and it's economical too!

The point of reference for xenon bulb replacement

- Replace one by one
- Xenon Vision perfectly matches the unchanged Xenon lamp

Xenon quality and ultra-resistant car bulb

- Philips is the inventor of Xenon HID technology
- Philips car lamps are highly UV resistant
- Philips car lamps are made of high-quality quartz glass
- Philips car lamps are highly resistant to humidity

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Award-winning car lamp manufacturer
- Complying with the high quality standards of ECE homologation

PHILIPS

Xenon car headlight bulb
Type of lamp: D4S Pack of: 1, 42 V, 35 W

Highlights

Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

ECE homologation

Philips automotive products and services are considered best in class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high-quality products and tested to the highest specifications, our products are designed to maximise the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

Award-winning car lamps



Our lamps are often rewarded by automotive experts

Economical choice

Thanks to its single lamp replacement technology Xenon Vision allows you to change your bulbs one by one while matching the colour temperature of the unchanged lamp. It is the most economical choice for lamp replacement.

Original Xenon technology



Xenon HID (High Intensity Discharge) lamps offer twice as much light for safer driving in all conditions. As a matter of fact, the intense white light produced by the Xenon HID lamps is comparable to daylight. Studies have demonstrated that xenon automotive lighting helps drivers to concentrate on the road and to distinguish obstacles and road signs much faster than traditional lamps.

42402VIC1

Single-lamp replacement

Philips Xenon Vision replaces a single burnt-out lamp while matching the colour of the unchanged one. Its new single-lamp replacement technology allows for one-by-one replacement while still matching the colour temperature of the unchanged lamp. Thus, Xenon Vision is the perfect solution for single-lamp replacement.

UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensuring their longevity

High-quality quartz glass

UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light.

Resistance to humidity

Only a burning bulb made of quartz glass can resist thermal shocks, such as a drop of cold water touching the hot bulb, which can happen when you drive through water with a broken headlight unit.

Xenon car headlight bulb
Type of lamp: D4S Pack of: 1, 42 V, 35 W

42402VIC1

Specifications

Packaging Data

- EAN3: 8727900364866
- EAN1: 8727900364859
- Packaging type: C1

Electrical characteristics

- Voltage: 42 V
- Wattage: 35 W

Lifetime

- Life time: Up to 2500 h

Light characteristics

- Colour temperature: 4400 K K
- Lumens: 3200 ±450 lm

Ordering information

- Order entry: 42402VIC1
- Ordering code: 36485933

Outer pack information

- Height: 5.7 cm
- Length: 11.1 cm

- Width: 9.6 cm
- Gross weight per piece: 0.094 kg

Product description

- Type: D4S
- Application: High beam, Low beam
- Designation: D4S Vision
- Homologation ECE
- Range: Vision
- Technology: Xenon
- Base: P32d-5

Packed product information

- Pack Quantity: 1
- MOQ (for professionals): 2
- Gross weight per piece: 45 g
- Height: 9.3 cm
- Length: 5.4 cm
- Net weight per piece: 18.1 g
- Width: 5.4 cm

Marketing specifications

- Expected benefits: More Vision
- Product highlight: Ideal for replacement



Issue date 2018-07-03

Version: 7.0.1

12 NC: 9285 345 24401
EAN: 87 27900 36485 9

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com