

PHILIPS

Headlight bulb

Ultinon HID 6000K

Type of lamp: D4S

Pack of: 2

42 V,35 W

42402WXX2



Drive with style

Instant upgrade to 6000K flash white light

Philips Ultinon HID (WX) is a 6000K white light Xenon HID bulb that enhances your style on the road

6000K flash white light for more style on the road

- Ultinon HID (WX) is the upgrade for your Xenon headlight

Maximum safety with Xenon HID

- Powerful light from Xenon HID bulb offers maximum safety

Original equipment manufacturer

- Philips is the choice of major car manufacturers
- Philips car lamps are made of high-quality quartz glass
- Philips car lamps are highly resistant against humidity
- Philips car lamps are highly UV resistant

Highlights

6000K Flash white upgrade

Philips Ultinon HID (WX) lamps are designed for drivers who want a stunning styling effect for their cars. The 6000K brilliant white light makes the car truly stunning compared to others.

Maximum safety with Xenon HID

Xenon HID (High Intensity Discharge) lamps offer twice as much light* for safer driving in all conditions. The intense white light produced by the Xenon HID lamps is comparable to daylight. Studies have demonstrated that xenon automotive lighting helps drivers to concentrate on the road and to distinguish obstacles and road signs much faster than traditional lamps. *compared to standard halogen bulbs

Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light

Resistance against humidity

Only a burning bulb made of quartz glass (filament 2650°C, glass 800°C) can resist thermal shocks : such as, if a drop of cold water touches the hot bulb, when you drive through water with a broken headlight unit.

UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensures their longevity

Specifications

Packaging Data

Packing: X2
EAN1: 8727900373318
EAN3: 8727900373325

Electrical characteristics

Voltage: 42 V
Wattage: 35 W

Lifetime

Life time: B3/Tc = 800/1500

Light characteristics

Color temperature: 6000 K
Light output: 2700 ±400 lumen

Marketing specifications

Expected benefits: Whiter light
Product highlight: 6000K

Outerpack information

Gross weight per piece: 1,15 kg
Height: 14 cm
Length: 35 cm
Width: 17,5 cm

Packed product information

Gross weight per piece: 115 g
Height: 7 cm
Length: 12,5 cm
Net weight per piece: 18,1 g
Pack Quantity / MOQ: 10
Width: 16 cm

Product description

Application: High beam, Low beam
Homologation ECE: NO
Marking ECE: N/A
Range: Ultinon HID - WX, Ultinon HID (WX), Ultinon HID 6000K
Technology: Xenon
Designation: D4S WX
Type: D4S

Ordering information

Ordering code: 37331828

