

PHILIPS

Headlight bulb

Xenon Vision

Type of lamp: D3S

Pack of: 1

42 V,35 W



42403VIS1



Feel safe, drive safe

Ideal for replacement

Philips Xenon Vision replaces a single burned-out lamp while matching the color of the unchanged one thanks to its new single-lamp replacement technology. Therefore it is the ideal replacement lamp and it's economical too!

The reference in case of xenon lamp replacement

- Replace one by one
- Xenon Vision perfectly matches the unchanged Xenon lamp

Xenon quality and ultra resistant car lamp

- Philips is the inventor of Xenon HID technology
- Philips car lamps are highly UV resistant
- Philips car lamps are made of high-quality quartz glass
- Philips car lamps are highly resistant against humidity

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Award winning car lamp manufacturer
- Respecting high quality standards of the ECE homologation

Highlights

Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

Rewarded Car lamps



Our lamps are often rewarded by automotive experts

Economical choice

Thanks to its single lamp replacement technology Xenon Vision allows you to change your bulbs one by one while matching the color temperature of the unchanged lamp. It is the most economical choice for lamp replacement.

Original Xenon technology



Xenon HID (High Intensity Discharge) lamps offer twice as much light for safer driving in all conditions. As a matter of fact, the intense white light produced by the Xenon HID lamps is comparable to daylight. Studies have demonstrated that xenon automotive lighting helps drivers to concentrate on the road and to distinguish obstacles and road signs much faster than traditional lamps.

Single-lamp replacement

Philips Xenon Vision replaces a single burned-out lamp while matching the color of the unchanged one. Its new single-lamp replacement technology allows for one-by-one replacement while still matching the color temperature of the unchanged lamp. Thus, Xenon Vision is the perfect solution for single-lamp replacement.

UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensures their longevity

High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light.

Resistance against humidity

Only a burning bulb made of quartz glass can resist thermal shocks : if a drop of cold water touches the hot bulb, which can happen when you drive through water with a broken headlight unit.

Specifications

Packaging Data

EAN3: 8727900364965
EAN1: 8727900364958
Packaging type: S1

Electrical characteristics

Voltage: 42 V
Wattage: 35 W

Lifetime

Life time: 2500h

Light characteristics

Lumens: 3200 ±450 lm
Color temperature: Up to 4300 K

Ordering information

Order entry: 42403VIS1
Ordering code: 36495833

Outerpack information

Gross weight per piece: 0.307 kg
Height: 14 cm
Length: 14.6 cm
Width: 13.1 cm

Product description

Type: D3S
Application: High beam, Low beam
Designation: D3S Vision
Homologation ECE

Range: Xenon Vision

Technology: Xenon

Base: PK32d-5

Packed product information

Pack Quantity: 1
MOQ (for professionals): 2
Gross weight per piece: 153.5 g
Height: 14 cm
Length: 12.5 cm
Net weight per piece: 67.5 g
Width: 6.8 cm

Marketing specifications

Expected benefits: More light
Product highlight: Ideal for replacement

