



Philips Ultinon HID 6000K
Headlight bulb

Type of lamp: D3S

Pack of: 2
42 V,35 W

42403WXX2



Drive with style

Instant upgrade to 6000K flash white light

Philips Ultinon HID (WX) is a 6000K white light Xenon HID bulb that enhances your style on the road

6000K flash white light for more style on the road

- Ultinon HID (WX) is the upgrade for your Xenon headlight

Maximum safety with Xenon HID

- Powerful light from Xenon HID bulb offers maximum safety

Original equipment manufacturer

- Philips is the choice of major car manufacturers
- Philips car lamps are made of high-quality quartz glass
- Philips car lamps are highly resistant against humidity
- Philips car lamps are highly UV resistant

PHILIPS

Headlight bulb
Type of lamp: D3S Pack of: 2, 42 V,35 W

Highlights

6000K Flash white upgrade

Philips Ultinon HID (WX) lamps are designed for drivers who want a stunning styling effect for their cars. The 6000K brilliant white light makes the car truly stunning compared to others.

Maximum safety with Xenon HID

Xenon HID (High Intensity Discharge) lamps offer twice as much light* for safer driving in all conditions. The intense white light produced by the Xenon HID lamps is comparable to daylight. Studies have demonstrated that xenon automotive lighting helps drivers to concentrate on the road and to distinguish obstacles and road signs much faster than traditional lamps. *compared to standard halogen bulbs

Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light

Resistance against humidity

Only a burning bulb made of quartz glass (filament 2650°c, glass 800°c) can resist thermal shocks : such as, if a drop of cold water touches the hot bulb, when you drive through water with a broken headlight unit.

UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensures their longevity

42403WXX2

Specifications

Packaging Data

- Packing: X2
- EAN1: 8727900373448
- EAN3: 8727900373455

Electrical characteristics

- Voltage: 42 V
- Wattage: 35 W

Lifetime

- Life time: B3/Tc = 800/1500

Light characteristics

- Color temperature: 6000 K
- Light output: 2700 ±400 lumen

Marketing specifications

- Expected benefits: Whiter light
- Product highlight: 6000K

Outerpack information

- Gross weight per piece: 1,15 kg
- Height: 14 cm
- Length: 35 cm
- Width: 17,5 cm

Packed product information

- Gross weight per piece: 150 g
- Height: 7 cm
- Length: 12,5 cm
- Net weight per piece: 75 g
- Pack Quantity / MOQ: 10
- Width: 16 cm

Product description

- Application: High beam, Low beam
- Base: PK32d-5
- Homologation ECE: NO
- Marking ECE: N/A
- Range: Ultinon HID - WX, Ultinon HID (WX), Ultinon HID 6000K
- Technology: Xenon
- Designation: D3S WX
- Type: D3S

Ordering information

- Ordering code: 37344828



Issue date 2020-02-03

Version: 11.0.1

12 NC: 8670 001 18822

© 2020 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

* Application varies per bulb type