



Philips Momentum
4K HDR display with
Ambiglow

Momentum

43 (42.51" / 108 cm diag.)
3840 x 2160 (4K UHD)



436M6VBPAB

Get in the moment

Experience a new level of entertainment immersion with the new Momentum 4K HDR display with Ambiglow lighting. An expansive 4K UHD display with DisplayHDR 1000 delivers ultra-crisp and vibrant image quality that will get you in the moment.

Expand your viewing experience

- UltraClear 4K UHD (3840x2160) resolution for precision
- MultiView enables simultaneous dual connection and view

Superb Picture Quality

- DisplayHDR 1000 for truly vivid details and realism
- Quantum Dot Tech for see-it-to-believe-it color

Brilliant performance

- Ambiglow intensifies entertainment with halo of light
- Enhanced audio with DTS Sound™
- Low input lag reduces time delay between devices to monitor
- Effortlessly smooth action with Adaptive-Sync technology

Designed for the way you work

- All your connections through one USB-C cable
- USB 3.0 Hub for convenient access and fast charging


PHILIPS

4K HDR display with Ambiglow
Momentum 43 (42.51" / 108 cm diag.), 3840 x 2160 (4K UHD)

436M6VBPAB/27

Highlights

UltraClear 4K UHD Resolution



These Philips displays utilize high performance panels to deliver UltraClear, 4K UHD (3840 x 2160) resolution images. Whether you are demanding professional requiring extremely detailed images for CAD solutions, using 3D graphics applications or a financial wizard working on huge spreadsheets, Philips displays will make your images and graphics come alive.

MultiView technology

With the ultra-high resolution Philips MultiView display you can now experience a world of connectivity. MultiView enables active dual connect and view so that you can work with multiple devices like a PC and notebook simultaneously, for complex multi-tasking.


VESA DisplayHDR 1000



VESA-certified DisplayHDR 1000 delivers a dramatically different visual experience vs. other 'HDR compatible' screens. Extreme deep blacks and bright whites contrast with brilliant colors, to bring out details that you've never experienced before. Gamers can spot enemies

hiding the dark corners and shadows easily, and movie viewers can enjoy a more compelling and lifelike show. This Philips Momentum comes with several HDR modes, each optimized for your usage scenarios: HDR Game, HDR Movie, and HDR Photo.

Quantum Dot Technology



Quantum Dot Technology is an innovative semiconductor nanocrystal technology that precisely emits light to produce bluer blues, greener greens and redder reds. LCD monitors with Quantum Dot color produce a more dynamic range of colors and show the true natural palette of colors in the picture. The result - vibrant, dynamic, you-gotta-see-it-to-believe-it color.

Ambiglow Technology



Ambiglow adds a new dimension to your viewing experience. The innovative Ambiglow technology enlarges the screen by creating an immersive halo of light. Its fast processor analyses the incoming image content and continuously adapts the color and brightness of


the emitted light to match the image. User friendly options allow you to adjust the ambiance to your liking. Especially suited for watching movies, sports or playing games, Philips Ambiglow offers you a unique and immersive viewing experience.

DTS Sound™



DTS Sound is an audio processing solution designed to optimize the playback of music, movies, streaming and games on the PC regardless of form factors. DTS Sound enables an immersive virtual surround sound experience, complete with rich bass and dialog enhancement and maximized volume levels free of any clipping or distortion.

Low Input Lag



Input lag is the amount of time that elapses between performing an action with connected devices and seeing the result on screen. Low input lag reduces the time delay between entering a command from your devices to monitor, greatly improve on playing twitch-sensitive video games, particularly important to whom plays fast-paced, competitive games.



Specifications

Picture/Display

- Adaptive sync
- LCD panel type: MVA
- Backlight type: B-LED+QD Film
- Panel Size: 42.51 inch / 108 cm
- Display Screen Coating: Anti-Glare, 3H, Haze 2%
- Color gamut (min.): BT. 709 Coverage: 100%*; DCI-P3 Coverage: 97.6%*
- Color gamut (typical): NTSC 119%*, sRGB 145%*
- HDR: DisplayHDR 1000 and UHDA certified
- Effective viewing area: 941.18 (H) x 529.42 (V)
- Aspect ratio: 16:9
- Optimum resolution: 3840 x 2160 @ 60 Hz
- Pixel Density: 103.64 PPI
- Response time (typical): 4 ms (Gray to Gray)*
- Brightness: 720 cd/m² (typical), 1,000 cd/m² (peak) nit
- Contrast ratio (typical): 4000:1
- SmartContrast: 50,000,000:1
- Pixel pitch: 0.245 x 0.245 mm
- Viewing angle: 178° (H) / 178° (V), @ C/R > 10
- Flicker-free
- Picture enhancement: SmartImage
- Display colors: 1.07 billion colors (10 bit*)
- Scanning Frequency: 23 - 80 Hz (V) / 30 - 160 kHz (H)
- sRGB
- LowBlue Mode

Connectivity

- Signal Input: HDMI 2.0 x 2, DisplayPort 1.4 x 1, mini DisplayPort 1.4 x 1, USB-C (DP Alt mode)
- USB: USB 3.0x2 (2 w/fast charging)*
- Sync Input: Separate Sync, Sync on Green
- Audio (In/Out): PC audio-in, Headphone out

Convenience

- Remote control type: Philips RC6 remote control
- Built-in Speakers: 7 W x 2 with DTS sound
- MultiView: PIP/PBP mode, 2x devices
- User convenience: Menu/OK, Input/Up, SmartImage Game/Return, Volume/Down, Power On/Off
- Control software: SmartControl
- OSD Languages: Brazil Portuguese, Czech, Dutch, English, Finnish, French, German, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Simplified Chinese, Spanish, Swedish, Traditional Chinese, Turkish, Ukrainian
- Other convenience: Ambiglow, Low Input Lag, Kensington lock, VESA mount (200x200mm)
- Plug & Play Compatibility: DDC/CI, Mac OS X, sRGB, Windows 10 / 8.1 / 8 / 7

Stand

- Tilt: -5/10 degree

Power

- On mode: 62.69 W (typ.) (EnergyStar 7.0 test method)
- Standby mode: 0.5 W (typ.)
- Off mode: 0.5 W (typ.)
- Power LED indicator: Operation - White, Standby mode- White (blinking)
- Power supply: Internal, 100-240VAC, 50-60Hz

Dimensions

- Product with stand (mm): 976 x 661 x 264 mm
- Product with stand in inch: 38.4 x 26.0 x 10.4 inch
- Product without stand (mm): 976 x 574 x 63 mm
- Product without stand in inch: 38.4 x 22.6 x 2.5 inch
- Packaging in mm (WxHxD): 1090 x 764 x 338 mm
- Packaging in inch (WxHxD): 42.9 x 30.1 x 13.3 inch

Weight

- Product with stand (kg): 14.71 kg
- Product with stand (lb): 32.36 lb
- Product without stand (kg): 13.96 kg
- Product without stand (lb): 30.71 lb
- Product with packaging (kg): 20.72 kg
- Product with packaging (lb): 45.58 lb

Operating conditions

- Temperature range (operation): 0 to 40 °C
- Temperature range (storage): -20 to 60 °C
- Relative humidity: 20%-80 %
- Altitude: Operation: +12,000ft (3,658m), Non-operation: +40,000ft (12,192m)
- MTBF: 50,000 hrs (excluding backlight) hour(s)

Sustainability

- Environmental and energy: EnergyStar 7.0, RoHS, WEEE
- Recyclable packaging material: 100 %
- Specific Substances: Mercury free, PVC / BFR free housing

Compliance and standards

- Regulatory Approvals: CE Mark, FCC Class B, RCM, BSMI, CB, CECP, cETLus, China RoHS, EAC, E-standby, ICES-003, J-MOSS, KC, KCC, KUCAS, Kuwait, PSB, PSE, SASO, SEMKO, TUV/ISO9241-307, UKRAINIAN, VCCI

Cabinet

- Color: Black
- Finish: Glossy / Textured

What's in the box?

- Monitor with stand
- Cables: USB-C cable, USB-A to USB-C cable, HDMI cable, DP cable, Power cable
- User Documentation
- Accessory: Remote control



Issue date 2022-07-14

Version: 10.0.1

12 NC: 8670 001 49606
UPC: 6 09585 25164 9

© 2022 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* Response time value equal to SmartResponse
* For Video transmission via USB-C, your Notebook/device must support USB-C DP Alt mode
* Fast charging complies with USB BC 1.2 standard
* BT. 709 / DCI-P3 Coverage based on CIE1976
* The monitor may look different from feature images.
* NTSC Area based on CIE1976
* sRGB Area based on CIE1931
* 10 bit is dithered by 8 bit with FRC