



Philips Signage Solutions  
D-Line Display

43"

UHD (3840 x 2160)  
500 cd/m<sup>2</sup>



43BDL4510D

## Say more

Smart, fast, 24/7 display.

Make it stand out with a fast Philips D-Line Professional 4K UHD display. Philips superb picture quality ensures true colours and intense contrast. You can effortlessly display content from multiple sources on a single screen.

### Brilliant picture. Blazing processor speed.

- Place in landscape or portrait orientation
- 4K UHD. Rich, deep images. Stunning contrast
- ADS wide-view panel display

### Operational flexibility

- SmartPower for energy saving

### Cost-effective system solution

- Energy-saving automatic backlight control
- FailOver ensures that content is always playing

### Effortless setup. Total control.

- Operate, monitor and maintain with CMND and Control
- Schedule what you want, when you want with SmartPlayer

# PHILIPS


# Highlights

## FailOver



From waiting room to meeting room, never show a blank screen. FailOver lets your Philips Professional Display switch automatically between primary and secondary inputs, ensuring that content keeps playing even if the primary source goes down. Simply set a list of alternative inputs to be sure your business is always on.


## SmartPower



The backlight intensity can be controlled and pre-set by the system to reduce the power


consumption by up to 50%, which saves substantially on energy costs.

## CMND and Control



Run your display network over a local (LAN) connection. CMND and Control allows you to perform vital functions like controlling inputs and monitoring display status. Whether you're in charge of one screen or 100.

## SmartPlayer



Turn your USB into a true cost-effective digital signage device. Simply save your content (video, audio, pictures) on your USB and plug into your display. Create your playlist and

schedule your content via the on-screen menu, and enjoy your own playlists anytime, anywhere.

## Energy saving

Energy-saving automatic backlight control

## Place in landscape

Place in landscape or portrait orientation

## 4K UHD. Rich, deep images

4K UHD. Rich, deep images. Stunning contrast

## ADS wide-view panel display

Be seen from any angle with ADS wide-view technology. Advanced Super Dimension Switch delivers faster on-display picture processing for smoother content transitions, remarkable image accuracy and superior colour reproduction with 180 degree viewing.

# Specifications

## Connectivity

- Audio output: 3.5 mm jack
- Video input: Display Port 1.2 (x 1), DVI-I (x 1), HDMI 2.0 (x 2), USB 2.0 (x 2)
- Audio input: 3.5 mm jack
- Video output: DisplayPort 1.2 (x 1), HDMI 2.0 (x 1)
- External control: RJ45, RS232C (in/out) 2.5 mm jack, IR (in/out) 3.5 mm jack

## Picture/Display

- Diagonal screen size (metric): 108.0 cm
- Diagonal screen size (inch): 42.5 inch
- Aspect ratio: 16:9
- Panel resolution: 3840 x 2160
- Pixel pitch: 0.2451 x 0.2451 mm
- Optimum resolution: 3840 x 2160 @ 60 Hz
- Brightness: 500 cd/m<sup>2</sup>
- Display colours: 1.07 G Billion
- Contrast ratio (typical): 1200:1
- Dynamic contrast ratio: 500,000:1
- Response time (typical): 8 ms
- Viewing angle (horizontal): 178 degree
- Viewing angle (vertical): 178 degree
- Picture enhancement: 3/2 - 2/2 motion pull down, 3D Combfilter, Motion compens. deinterlacing, 3D MA deinterlacing, Dynamic contrast enhancement, Progressive scan
- Panel technology: ADS

## Convenience

- Placement: Landscape (24/7), Portrait (24/7)
- Screen-saving functions: Pixel Shift, Low Bright
- Keyboard control: Hidden, Lockable
- Signal loop through: RS232, IR Loop through, DisplayPort, HDMI
- Energy-saving functions: Smart Power
- Network controllable: RS232, RJ45

## Sound

- Built-in speakers: 2 x 10 W RMS

## Power

- Mains power: 100 ~ 240 VAC, 50 ~ 60 Hz
- Consumption (Typical): 90 W
- Consumption (Max): 150 W
- Standby power consumption: 0.5 W
- Energy Label Class: G

## Supported Display Resolution

- Computer formats: 1920 x 1080, 60 Hz, 1024 x 768, 60 Hz, 1280 x 1024, 60 Hz, 1280 x 720, 60 Hz, 1440 x 900, 60 Hz, 1600 x 900, 60 Hz, 1680 x 1050, 60 Hz, 3840 x 2160, 30, 60 Hz, 640 x 480, 60 Hz, 800 x 600, 60 Hz
- Video formats: 1080i, 50, 60 Hz, 576i, 50 Hz, 576p, 50 Hz, 480p, 60 Hz, 480i, 60 Hz, 1080p, 50, 60 Hz, 2160p, 24, 30, 60 Hz, 720p, 50, 60 Hz

## Dimensions

- Set Width: 973.0 mm
- Product weight: 10.71 kg
- Set Height: 561.2 mm
- Set Depth: 63.5 mm
- Set Width (inch): 38.31 inch
- Set Height (inch): 22.09 inch
- Wall Mount: 200 (H) x 200 (V) mm, M6
- Set Depth (inch): 2.50 inch
- Bezel width: 13.9 mm (Even bezel)
- Product weight (lb): 23.61 lb

## Operating conditions

- Altitude: 0 ~ 3000 m
- Temperature range (operation): 0 ~ 40 °C
- MTBF: 50,000 hour(s)
- Temperature range (storage): -20 ~ 60 °C
- Humidity range (operation)[RH]: 20–80% RH (No condensation)
- Humidity range (storage) [RH]: 5–95% RH (No condensation)

## Multimedia Applications

- USB Playback Video: MPEG, H.263, H.264, H.265, VP8
- USB Playback Picture: BMP, JPEG, PNG
- USB Playback Audio: AAC, HEAAC, MPEG

## Accessories


- Included accessories: Quick start guide, RS232 cable, AC Power Cord, HDMI cable, Remote Control and AAA Batteries
- Included Accessories: RS232 daisy-chain cable, Philips logo (x 1), Screws, USB Cover (x 1), AC Switch Cover
- Stand: BM05922(Optional)

## Miscellaneous

- On-Screen Display Languages: English, French,

- German, Spanish, Polish, Turkish, Russian, Italian, Simplified Chinese, Traditional Chinese, Arabic, Japanese, Danish, Dutch, Finnish, Norwegian, Portuguese, Swedish
- Warranty: 3 year warranty
- Regulatory approvals: CE, CCC, BSMI, CB, VCCI, CU, EMF, ETL, FCC, Class A, PSB, RoHS

Philips 43BDL4550D  
Version: 3.1  
Release Date: 2020/08/11



Issue date 2024-03-24

Version: 3.0.1

EAN: 87 12581 76885 0

© 2024 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)