



Philips  
5000 series Smart Ultra  
HDTV with Net TV and  
High Dynamic Range

**43" class/po**  
4K Ultra HD 2160p  
HDR  
Wireless LAN 802.11ac MIMO



**43PFL5703**

## Smart 4K UltraHDTV

Your favorite online content in UltraHD

Enjoy true 4K streaming performance with built-in HEVC and VP9 decoders enabling 4K streaming on Netflix, YouTube and more services in the future. With a 4K upscaling engine, even your HD videos have never looked better.

### Enjoy the beauty of 4K Ultra HD

- The beauty of 4K UltraHD TV is in savoring every detail
- Pixel Plus UltraHD for vivid, natural, and real pictures
- 120 Perfect Motion Rate for increased pixel response times
- An intelligent dimming backlight for dynamic contrast
- Enjoy HD content in 4K UHD with a 4K upscaling engine
- Expanding the possibilities of visual perception

### Authentic and clear sound experience.

- 16 Watts of clear balanced surround sound
- Immersive sound with clear voice designed by sonic emotion
- Dolby Audio for the ultimate movie experience

### Complete digital TV connectivity made simple.

- Wireless LAN 802.11ac with MIMO for seamless streaming of 4K
- Wirelessly mirror the screen of smart device on your TV
- NetTV with Wireless access to online services on your TV



# PHILIPS

# Highlights

## 4K UltraHD



4 times the resolution of Full HD brings your viewing experience to the whole new level. Enjoy every detail and the breathtaking beauty of the pictures.

## High Dynamic Range



High Dynamic Range (HDR10) is a technology lets you experience more detail and captivating colors for an even more engaging television experience. More perceivable shades of blacks, whites and all other colors. This boils down to greater perceived brightness and contrast with darker shadows creating a breathtaking image.


## Pixel Plus Ultra HD



Experience Ultra-HD sharpness from Philips. Now you can enjoy your favorite action films

and sporting events in stunning 4K Ultra HD resolution. And whether you stream online or watch a DVD, Philips' Pixel Plus Ultra-HD Engine delivers sharper images with brighter whites and blacker blacks.

## Bright Pro



BrightPro backlight boosts brighter areas of the image by up to twice as much as a regular LED backlight. Bright Pro enables to display exceptional brightness and contrast even in brightly lit rooms. Video scenes which feature bright light sources such as sunlight, fireworks, police lights, flashlights, etc. look more realistic and lifelike.

## Macro dimming




Using a proprietary video processing algorithm which measures average luminance level of each video frame, Philips' Macro Dimming intelligent backlight dims the backlight to match every video frame to ensure you have a strain-free life-like viewing experience with bright whites, vivid colors and dark blacks.

## 120 Perfect Motion Rate



120 Perfect Motion Rate (PMR) creates extreme motion sharpness for clear and vibrant images in fast action movies. The new Philips PMR standard reduces response time of the HDTV to produce faster picture transitions and reduces motion artifacts.

## Net TV



Philips NetTV is built for streaming. With a simple push of a button, gain instant access to popular streaming applications such as Netflix, Vudu, YouTube, all within a clutter-free, easy to use interface. Visit the App Store to download additional content from our extensive entertainment library, with entertainment options to suit everyone. Surf the web on your big screen TV, all without the need of connecting a computer. Enjoy smooth streaming of up-to 4K content with the powerful, built-in Wireless 802.11ac MIMO Dual-Band chipset.

# Specifications

## Picture/Display

- Aspect ratio: Widescreen(16:9)
- Contrast ratio (typical): 1000:1
- Response time (typical): 9 ms
- Viewing angle: 178° (H) / 178° (V)
- Diagonal screen size: 43 inch / 109.22 cm
- Visible screen diagonal (inch): 43 inch
- Display screen type: LED UltraHD Display
- Panel resolution: 3840x2160p
- Picture enhancement: Pixel Plus UltraHD, Black stretch, Digital Noise Reduction, MPEG artifact reduction, 120 PMR, Color Enhancement, Dynamic contrast, Gamma, Macro Dimming

## Supported Display Resolution

### • Computer formats

Resolution	Refresh rate
640 x 480	60Hz
720 x 480	60Hz
800 x 600	60Hz
1024 x 768	60Hz
1280 x 768	60Hz
1280 x 1024	60Hz
1360 x 768	60Hz
1440 x 900	60 Hz
1920 x 1080	60Hz
1680 x 1050	60Hz
1400 x 1050	60Hz
3840 x 2160	60Hz
4096 x 2160	60Hz

### • Video formats

Resolution	Refresh rate
480i	60Hz
480p	60Hz
720p	60Hz
1080i	60Hz
1080p	24,30,60Hz
2160p	24, 30, 60Hz

## Sound

- Equalizer: 5-bands
- Output power (RMS): 2 x 8W
- Sound System: Sonic Emotion Premium, Stereo, SAP, Dolby Audio

## Loudspeakers

- Built-in speakers: 2

## Convenience

- Child Protection: Child Lock+Parental Control
- Clock: Sleep Timer
- Ease of Installation: Autostore
- Ease of Use: AutoPicture, AutoSound, Settings assistant Wizard, Auto Volume Leveling
- Remote Control: TV
- Screen Format Adjustments: 4:3, Movie expand 14:9, Movie expand 16:9, Super Zoom, Widescreen, unscaled (1080p dot by dot), Full, Automatic
- Multimedia: auto slideshow, USB media browser

## Multimedia Applications

- Multimedia connections: USB Storage Device
- Playback Formats: MP3, JPEG Still pictures, MPEG1, MPEG2, H.264/MPEG-4 AVC, H.265/HEVC, AAC, WAVE, AC3, MPEG4

## Tuner/Reception/Transmission

- Aerial Input: 75 ohm F-type
- TV system: ATSC, NTSC
- Video Playback: NTSC
- Tuner bands: UHF, VHF

## Connectivity

- AV 1: Shared audio L/R in, CVBS/YPbPr
- Audio Output - Digital: Optical (TOSLINK)
- Other connections: Ethernet, Headphone out, Wireless LAN 802.11ac MIMO
- USB: USB
- HDMI 1: Shared audio L/R in, HDMI
- HDMI 2: Shared audio L/R in, HDMI (Audio Return Channel)
- HDMI 3: HDMI, Shared audio L/R in
- EasyLink (HDMI-CEC): One touch play, Power status, System info (menu language), Remote control pass-through, System audio control, System standby

## Power

- Ambient temperature: 5°C to 40°C (41°F to 104°F)
- Mains power: 120V/60Hz

- Power consumption: 90 W
- Standby power consumption: < 0.5W

## Dimensions

- Set dimensions in inch (W x H x D): 38.1 x 22.7 x 3.4 inch
- Product weight (lb): 16.8 lb
- Set dimensions with stand in inch (W x H x D): 38.1 x 23.9 x 7.3 inch
- Product weight (+stand) (lb): 17.0 lb
- Box dimensions in inch (W x H x D): 41.7 x 25.6 x 6.4 inch
- Weight incl. Packaging (lb): 22.5 lb
- VESA wall mount compatible: 300 x 200 mm

## Accessories

- Included accessories: Table top stand, Quick start guide, User Manual, Remote Control, Screws, Batteries for remote control
- Power cord: 59.05 inch

## Network Services


- NetTV Apps: Netflix, Vudu, Vewd browser, YouTube, Pandora, Vewd app store, Youtube TV, Showtime Streaming
- Network Features: Home Network, Wireless Screencasting

## Connections

### Side



### Rear



Issue date 2018-08-15

Version: 2.1.1

12 NC: 8670 001 53453  
UPC: 6 09585 25204 2

© 2018 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)