



Philips Signage Solutions
Video Wall Display

49"

Direct LED Backlight
Full HD
450 cd/m²

SignageSolutions

49BDL3005X

Go big

Versatile videowall display.

Command attention with a Philips X-Line Professional Videowall Display. Crisp contrast and narrow bezels enable clear, distraction-free imaging. Whether you're running an airport or hosting a conference.

Brilliant images. Endless possibilities.

- Full HD monitors. Brilliant images. Clear contrast
- IPS panel: rich colour consistency from every angle
- Ultra-narrow (3.5 mm) bezels. For distraction-free images

Effortless setup. Total control.

- Add Android processing power with an optional CRD50 module
- Operate, monitor and maintain with CMND and Control

Powerful system solution

- Tiling mode. Create tiled 4K videowalls of any size
- FailOver ensures that content is always playing
- OPS slot allows for PC embedding without cabling
- Energy-saving automatic backlight control

PHILIPS

Video Wall Display
49" Direct LED Backlight, Full HD, 450 cd/m²

Highlights

Tiling mode


Connect two or more Philips professional displays to create a tiled videowall — without the need for external devices. A single player takes care of content, whether you have four screens or 40. 4K content is fully supported and if you're showing that content on four screens you get the best possible dot-by-dot resolution.

Optional CRD50 module

Embed an Android System-on-Chip (SoC) into your Philips Professional Display. The optional CRD50 module is an OPS device that enables

Android processing power without the need for cables. Simply slide into the OPS slot, which contains all the connections needed to run the module (including power supply).

CMND and Control




Run your display network over a local (LAN) connection. CMND and Control allows you to perform vital functions like controlling inputs

49BDL3005X/00

and monitoring display status. Whether you're in charge of one screen or 100.

OPS slot



Integrate a full-power PC or Android-powered CRD50 module directly into your Philips Professional Display. The OPS slot contains all the connections you need to run your slot-in solution, including a power supply.

Specifications

Picture/Display

- Diagonal screen size: 48.5 inch / 123.2 cm
- Panel resolution: 1920 x 1080p
- Optimum resolution: 1920 x 1080 @ 60 Hz
- Brightness: 450 cd/m²
- Contrast ratio (typical): 1300:1
- Dynamic contrast ratio: 500,000:1
- Response time (typical): 8 ms
- Aspect ratio: 16:9
- Viewing Angle (H / V): 178 / 178 degree
- Pixel pitch: 0.56 x 0.56 mm
- Display colours: 1073 M
- Picture enhancement: 3/2 - 2/2 motion pull down, 3D Combfilter, Motion compens. deinterlacing, Progressive scan, 3D MA deinterlacing, Dynamic contrast enhancement

Supported Display Resolution

• Computer formats

Resolution	Refresh rate
3840 x 2160	30Hz
1920 x 1200	60 Hz
1920 x 1080	60 Hz
1600 x 1200	60 Hz
1440 x 900	60 Hz
1366 x 768	60 Hz
1360 x 768	60 Hz
1280 x 1024	60 Hz
1280 x 800	60 Hz
1280 x 768	60 Hz
1024 x 768	60 Hz
800 x 600	56, 60, 72, 75 Hz
640 x 480	60, 67, 72, 75 Hz

• Video formats

Resolution	Refresh rate
2160p	30 Hz
1080p	50, 60 Hz
1080i	50, 60 Hz
720p	50, 60 Hz
576p	50 Hz
576i	50 Hz
480p	60 Hz
480i	60 Hz

Connectivity

- Video input: DVI-D, HDMI (x 2), VGA (Analogue D-Sub), DisplayPort (1.2), Component (BNC x 3), Composite (BNC)
- Video output: DisplayPort, DVI-I, VGA (via DVI-I)

- Audio input: 3.5 mm jack, Audio Left/Right (RCA)
- Audio output: Audio Left/Right (RCA), External speaker connector
- External control: IR (in/out) 3.5 mm jack, RJ45, RS232C (in/out) 2.5 mm jack
- Other connections: OPS

Convenience

- Signal loop through: RS232, VGA, DisplayPort, DVI, IR Loop through
- Ease of installation: Carrying Handles
- Energy-saving functions: Smart Power
- Network controllable: RS232, Card OPS RS232, RJ45, One Wire (HDMI-CEC)
- Placement: Landscape (24/7), Portrait (24/7)
- Screen-saving functions: Pixel Shift, Low Bright
- Tiled Matrix: Up to 10 x 10

Dimensions

- Bezel thickness: 3.5 mm
- Bezel width: Top/Left: 2.35 mm, Bottom/Right: 1.25 mm
- Set dimensions (W x H x D): 1077.6 x 607.8 x 103.8 mm
- Set dimensions in inch (W x H x D): 42.4 x 23.9 x 4.1 inch
- VESA Mount: 400 x 400 mm, M6
- Product weight: 21.6 kg
- Product weight (lb): 47.6 lb

Operating conditions

- Temperature range (operation): 0 ~ 40 °C
- Temperature range (storage): -20 ~ 60 °C
- Altitude: 0 ~ 3000 m
- Relative humidity: 20 ~ 80 %
- MTBF: 60,000 hour(s)

Power

- Consumption (On mode): 110 W (EnergyStar 6.0 test method)
- Standby power consumption: <0.5 W
- Energy Label Class: G

Sound

- Built-in speakers: 2 x 10 W (RMS)

Accessories


- Included Accessories: IR cable, IR sensor cable (1.8 m) (x 1), RS232 daisy-chain cable, RS232 DB9

- adapter cable, Thumb Screw
- Included accessories: Remote Control, Batteries for remote control, AC Power Cord, Quick start guide, Edge alignment pins, Edge alignment plates, DVI-D cable
- Optional accessories: Edge finishing kit, ColourCalibrationKit (CCK4602), IR Light Motion Sensor (CRD41)

Miscellaneous

- On-Screen Display Languages: Arabic, Simplified Chinese, Traditional Chinese, English, French, German, Italian, Japanese, Polish, Russian, Spanish, Turkish
- Regulatory approvals: CE, FCC, Class B, UL/cUL, CB, GOST, EPEAT
- Warranty: 3 year warranty

Philips 49BDL3005X
Version: L1
Release Date: 2019/02/22



Issue date 2021-03-04

Version: 3.1.1

12 NC: 8670 001 58797
EAN: 87 12581 75787 8

© 2021 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com