

Philips 8000 series
LED TV with Ambilight
Spectra 2 and Perfect Pixel
HD Engine

132 cm (52")

Full HD 1080p
digital TV

52PFL8605H



Refined living, pure performance

with Ambilight and leading picture

Top performance on a picture perfect 132 cm (52") flat screen. The Philips 52PFL8605 LED TV provides a frameless design with Ambilight to set the scene for you to experience the brilliance of LED lighting technology. Enjoy the show.

Enlarge your viewing experience

- Ambilight Spectra 2 widens the viewing experience

Perfect LCD Picture

- Full HD with Perfect Pixel HD Engine for unrivalled clarity
- Full HD 3D Ready for a truly immersive 3D movie experience
- Brilliant LED images with low power consumption
- 200Hz Clear LCD TV, 1ms performance: superb motion sharpness
- Perfect Natural Motion for ultra smooth Full HD movies

Impressive, invisible sound

- Feel the power of 20W RMS and Incredible Surround

In-built internet TV

- Philips Net TV for popular online services on your TV

Greener every day

- LED TVs up to 40% more energy efficient than normal LCD TVs



PHILIPS

LED TV
132 cm (52") Full HD 1080p, digital TV

52PFL8605H/12

Highlights

Ambilight Spectra 2



Add a new dimension to your viewing experience with Ambilight Spectra 2. This patented Philips technology enlarges the screen by projecting a glow of light, on the 2 sides of the TV, from the back of the screen onto the surrounding wall. Ambilight adjusts automatically the colour and brightness of the light to match the picture, creating an immersive viewing experience. The wall adaptive function ensures that the color of the light always matches the picture, no matter what the color of your wall. With Ambilight Spectra 2 movies truly come to life!

Perfect Pixel HD Engine

Experience unrivalled sharpness and clarity with Perfect Pixel HD Engine. Each pixel of the picture is enhanced to better match the surrounding pixels, for a more natural picture. The result is a unique combination of sharpness, natural detail, vivid colors, superior contrast and smooth natural motion whatever you are watching. Clean and razor sharp images result from artifact and noise detection and reduction in all content sources - from multimedia to standard TV. The Full HD screen with 1920 x 1080p pixels produces brilliant flicker-free progressive scan pictures with superb brightness.

Full HD 3D Ready



Be enthralled by 3D movies in your own living room with the Full HD 3D ready TV. Active 3D uses the latest generation of fast switching displays for real life depth and realism in full 1080x1920 HD resolution. Premium 3D movie releases on BluRay and upcoming 3D broadcast offers a wide and high quality content selection. Your TV is ready for the Full HD 3D experience by adding a 3D compatible BluRay player or HD receiver, and the accessory 3D upgrade kit (Philips PTA02). For family enjoyment with more than 2 viewers add as many 3D glasses as you wish (extension kit PTA03).

LED



The most advanced LED lighting technology in this TV combines an eye-catching minimalistic design with stunning image quality as well as the lowest power consumption in its category. On top of that, LED lighting technology does not contain any hazardous materials. Thus, with LED backlight you can enjoy low power

consumption, high brightness, incredible contrast, sharpness and vibrant colors.

Energy Class A

EU Energy Label
EU Energy Label. For many years Philips has pro-actively been working on the reduction of both on-mode and standby power consumption of its televisions. As a result most Philips televisions have achieved green EU energy labels in 2010/2011. The greener the label, the lower the on-mode power consumption the lower your energy bill and friendlier to the environment.



Matching home theatre experience

Intensify your cinematic viewing experience further with the matching Philips Soundbar (HTS9140). You now only need one remote control to operate both devices. Using Philips Easylink via HDMI connection, you are also ensured that you have the best picture and sound performance from the complete combination. Enquire more about this unique combination today!



Perfect
Pixel
HD ENGINE



200Hz
CLEARLCD | 1



Full HD
1080p



Specifications

Picture/Display

- Aspect ratio: Widescreen
- Brightness: 450 cd/m²
- Dynamic screen contrast: 500000:1
- Response time (typical): 1 (BEW) ms
- Viewing angle: 176° (H) / 176° (V)
- Diagonal screen size: 52 inch / 132 cm
- Display: LCD Full HD, edge LED backlight
- Panel resolution: 1920x1080p
- Picture enhancement: Perfect Pixel HD Engine, Perfect Natural Motion, Perfect Contrast, Perfect Colors, Active Control + Light sensor, 2D/3D noise reduction, 200Hz Clear LCD, Super Resolution, 3D TV prepared^{8*}
- Screen enhancement: Anti-Reflection coated screen
- Peak Luminance ratio: 65 %
- Color processing: 2250 trillion colors 17bit RGB
- 3D: 3D Ready^{*}
- Color cabinet: Seamless front glass

Ambilight

- Ambilight Version: 2 sided
- Ambilight Features: Ambilight Spectra 2, Lounge light mode in stand-by, 'Sunset' soft switch off, Wall colour adaptive
- Dimming Function: Manual and via Light Sensor
- Ambilight light system: LED wide color

Supported Display Resolution

- Computer inputs: up to 1920x1080 @ 60Hz
- Video inputs: up to 1920x1080p, 24, 25, 30, 50, 60 Hz

Sound

- Output power (RMS): 2 x 10W, Invisible Sound
- Sound Enhancement: Auto Volume Leveller, Dynamic Bass Enhancement, Incredible Surround, Treble and Bass Control, Clear Sound

Convenience

- Ease of Installation: Channel installation wizard, Network installation wizard, Settings assistant wizard, Device connection wizard, Auto detect Philips devices, 2-in-1 Wallmount Stand
- Ease of Use: Onscreen Usermanual, Touch control

buttons, Favorite program selection, Mozaic channel grid, One-stop experience button, One-stop Home button

- Electronic Program Guide: Now + Next EPG, 8day Electronic Program Guide^{*}
- Screen Format Adjustments: Autofill (no black bars), Autozoom (original format), (includes 4:3, 14:9, 21:9), Super Zoom, Movie expand 16:9, Widescreen, unscaled (1080p dot by dot)
- Teletext: 1200 page Hypertext
- Firmware upgradeable: Firmware auto upgrade wizard, Firmware upgradeable via USB, Online firmware upgrade
- Multimedia: DLNA media Browser, Net TV services, USB media browser

Multimedia Applications

- Picture Playback Formats: JPEG
- Music Playback Formats: MP3, WMA (v2 up to v9.2), AAC
- Video Playback Formats: Codec support:, H264/ MPEG-4 AVC, MPEG-1, MPEG-2, MPEG-4, WMV9/ VC1, Containers: AVI, MKV
- Net TV: Included

Tuner/Reception/Transmission

- Aerial Input: 75 ohm coaxial (IEC75)
- Video Playback: NTSC, SECAM, PAL
- Digital TV: DVB Terrestrial ^{*}, DVB-T MPEG4^{*}, DVB-C MPEG4^{*}, MHEG
- Tuner bands: Hyperband, S-Channel, UHF, VHF

Connectivity

- Ext 1 Scart: Audio L/R, CVBS in, RGB
- Ext 2 Scart: Audio L/R, CVBS in, RGB
- Ext 3: YPbPr, Audio L/R in
- VGA-in: PC input, D-sub 15
- HDMI 1: HDMI v1.4 (Audio Return Ch.)
- HDMI 2: HDMI v1.3
- HDMI 3: HDMI v1.3
- HDMI Side: HDMI v1.3
- Front / Side connections: USB, Common Interface Slot (CI-CI+), SD-card (Videostore)
- Other connections: Headphone out, S/PDIF out (coaxial), Ethernet-LAN RJ-45, 3D TV connector

- HDMI features: Audio Return Channel, Instaport fast HDMI switching
- EasyLink (HDMI-CEC): One touch play, EasyLink, Pixel Plus link (Philips), Remote control pass-through, System audio control, System standby
- PC network link: DLNA 1.5 certified
- Summary: 4x HDMI, 1x USB, 2x SCART, 1x Ethernet, Wi-Fi ready

Power


- Green label: ECO label certified
- Ambient temperature: 5 °C to 35 °C
- Mains power: 220 - 240V, 50/60Hz
- Power consumption (typical): 94.0 W
- Standby power consumption: <0.15 W
- Off mode power consumption: < 0.01 W
- Annual energy consumption: 137.24 kWh
- Presence of lead: Yes^{*}
- Power Saving Features: 0 Watt Power-off switch, Light sensor, Eco mode, Picture mute (for radio), Auto switch-off timer, Eco settings menu

Dimensions

- Set dimensions (W x H x D): 1245 x 757 x 51 mm
- Set dimensions with stand (H x D): 802 x 268 mm
- Stand width: 508 mm
- Product weight: 33 kg
- Product weight (+stand): 36 kg
- VESA wall mount compatible: 400 x 400 mm

Accessories

- Included accessories: Power cord, Quick start guide, Warranty certificate, Remote Control, Batteries for remote control, Legal and safety brochure, Net TV brochure
- Optional accessories: Wireless USB adaptor (PTA01), 3D TV extension kit (PTA03), 3D TV starter kit (PTA02)



Issue date 2019-06-26

Version: 8.1.10

12 NC: 8670 000 59591
EAN: 87 12581 52293 3

© 2019 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

^{*} 8 days EPG, service not available in all countries

^{*} Net TV: Visit www.philips.com/smarty to discover the services offering in your country.

^{*} The TV supports DVB reception for 'Free to air' broadcast. Specific DVB operators may not be supported. An up to date list can be found in the FAQ section of the Philips support website. For some operators Conditional Access and subscription are required. Contact your operator for more information.

^{*} 3D TV requires Accessory PTA02 (Active shutter glasses and transmitter, a 3D compatible source device, and 3D source material.

^{*} Typical on-mode power consumption measured according to IEC62087 Ed 2.

^{*} Annual energy consumption is calculated using the typical power consumption 4 hours per day, 365 days per year.

^{*} This television contains lead only in certain parts or components where no technology alternatives exist in accordance with existing exemption clauses under the RoHS Directive.