



Philips Ultinon LED  
Interior car light

**6418WLED-WHITE**

Number of bulbs: 1  
12 V, 6000 K daylight effect  
Experience more light



**6418ULWX1**

## Bright interior lighting

See more with LED lighting

Never lose your keys again with bright, stylish and durable Philips 6418WLED (38MM Festoon) interior lighting. Strong light illuminates the inside of your car, while being kind on your eyes.

### **Stylish look**

- Bright interior lights to see everything inside your car
- Upgrade your lights, upgrade your style

### **Bright LED interior lights**

- Durable and long-lasting LED lighting

### **Long lasting LED lights**

- Instant-on Performance
- Good light distribution for enhanced visibility

### **Good light diffusion**

- Philips automotive lighting at the highest quality level

### **Durable Philips quality**

- Easy installation and compatible with many car models
- Durable and long-lasting LED lighting

# PHILIPS

## Interior car light

6418WLED-WHITE Number of bulbs: 1, 12 V, 6000 K daylight effect, Experience more light

# Specifications

### Packaging Data

- EAN1: 46678721380
- EAN3: 50046678721385
- Packaging type: X1

### Product description

- Technology: LED
- Application: Interior, glove box, dome, trunk
- Range: Ultinon LED
- Type: Festoon 38mm
- Homologation ECE: NO
- Base: SV8,5
- Designation LED Type: 6418WLED-WHITE

### Electrical characteristics

- Voltage: 12 V

### Marketing specifications

- Expected benefits: Experience more light
- Product highlight: Stylish interior light

### Light characteristics

- Color temperature: Up to 6000K
- Lumens [lm]: 45

### Ordering information

- Order entry: 6418ULWX1
- Ordering code: 78721385

### Outerpack information

- Gross weight per piece [lbs]: 1.32
- Height [in]: 3.54
- Length [in]: 7.87
- Width [in]: 5.91

### Packed product information

- MOQ (for professionals): 10
- Pack Quantity: 1
- Gross weight per piece [lbs]: 0.01
- Height [in]: 3.54
- Length [in]: 2.76
- Width [in]: 1.18

### Lifetime

- Life time: Up to 8 years

6418ULWX1

# Highlights

### Stylish interior light

Your light requirements and taste may differ depending on the application. For the interior of your car, you can select from a variety of colors of Philips Ultinon LED lamps for more stylish look. Select either cool blue light or the bright white light of 6000 Kelvin. Your car is an expression of who you are, so make a style statement with Philips interior LED lights.

### See more inside your car

Whether it's your phone, your keys or your child's missing left shoe, at some point we've all had to search for a misplaced item in a poorly lit car. With Philips LED interior lighting, you get a bright, white, and uniformly diffused light. So the next time you're searching around in the trunk, the glove compartment or the floor of your car, you'll be able to see exactly what you're doing and find anything with ease.

### Long-lasting LED lighting

You want bright and stylish car lights. But you don't want to keep replacing failed lamps. That is a major weakness of conventional lights: the more powerful the light, the shorter its lifespan. At the same light intensity, LEDs last longer. And Philips Ultinon LED lights have additional resistance to heat and vibration, making them a perfect choice for long-lasting performance, with a lifetime of up to 8 years.

### Good light diffusion

Philips LED interior lighting range is designed to ensure the light is evenly distributed in the car's interior. You'll have an easier time seeing what's inside in a faster amount of time.

### Automotive grade quality

The technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. The Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful bright light, and precise beam performance. You get high-end style.

### Ready, steady, installed!

Designed to be easily installed in compatible vehicles, drivers with maintenance experience will be able to upgrade compatible lights with ease.

### Long-lasting LED lighting

Your car is an expression of who you are. Make a statement and get noticed with durable and long-lasting Philips Ultinon LEDs. They are a direct replacement for conventional bulbs, easy to install and available for a wide range of interior and exterior applications.

### Excellent Light Distribution

The bright output and intense color adds more than just style. They provide superior light distribution, with a wide angle beam on the road so you can see and be seen better.



Issue date 2019-01-31

Version: 4.1.1

12 NC: 8670 001 50262

© 2019 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)

\* It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.