THE ALL NEW CAR
CONFIGURATOR.
CHOOSE YOUR PERFECT COLOR

Philips Signage Solutions Q-Line Display

65"

Direct LED Backlight Full HD

65BDL3000Q

Intensify your signage experience

With priceless performance

Deliver startlingly clear images in a more eco-friendly way with the Q-Line display. High on performance and reliability, yet low on power consumption, it is ideal for projects where no compromise is accepted.

Optimized for public viewing

• Full HD LED for brilliant images with incredible contrast

Innovative solutions for any signage application

- Connect and control your content via the cloud with HTML5
- Schedule what you want, when you want with SmartPlayer
- CMND: Take control of your displays
- Create and update content with CMND & Create

Care about you, your business and your audience

- SmartPower for energy saving
- · Keep your content up and running with FailOver
- Manage settings of multiple displays with CMND & Control
- Simplify meetings with FailOver for conferencing



Highlights

CMND



A robust display management platform, CMND puts the power back into your hands. Update and manage content with CMND & Create or control your settings with CMND & Control. It's all possible with CMND.

CMND & Control



With CMND & Control, easily manage multiple displays in a central location. With real time display monitoring, setting and software updates from a remote location, and the ability to customize and configure multiple displays at once, such as video wall or menu board displays, controlling your suite of displays has never been easier.

SmartPlayer



Turn your USB into a true cost effective digital signage device. Simply save your content (video, audio, pictures) on your USB and plug into your display. Create your playlist and schedule your content via the on screen menu, and enjoy your own created playlists anytime, anywhere.

FailOver



Keeping your content up and running is critical for demanding commercial applications. While it is unlikely you will face a content disaster, FailOver provides content protection with a revolutionary technology that plays back-up content on screen in the event of a media player failure. FailOver automatically kicks in when the primary input fails. Simply select a primary input connection and a FailOver connection and your ready for instant protection.

FailOver for Meeting Rooms

Using FailOver, simplify your presentations and videoconferencing. When a meeting or conference room is not in use, background content can run from whatever input source you choose. When the meeting starts and you need to share a presentation or your screen, simply connect your computer and the display automatically switches inputs and shows what's on your screen, with no need to manually switch inputs.

SmartPower



The backlight intensity can be controlled and pre-set by the system to reduce the power

consumption by up to 50%, which saves substantially on energy costs.

Full HD LED technology

Picture Quality matters. Regular displays deliver quality, but you expect more. Imagine crisp detail paired with high brightness, incredible contrast and realistic colors for a true to life picture.

SmartBrowser



Connect and control your content via the cloud with the integrated HTML5 browser. Design your signage content online and connect it with a display or with your complete network. Simply plug in a RJ45 internet cable for network connection, connect the display with the dedicated url-address and you are ready to play your cloud based content.

CMND & Create

Design and create compelling content with CMND & Create, a powerful authoring tool. With a drag and drop interface, preloaded templates, and integrated widgets, you'll be able to amaze your customers with compelling content.

















Warranty: 3 year warranty

On-Screen Display Languages: Arabic, Simplified

German, Italian, Polish, Russian, Spanish, Turkish,

Chinese, Traditional Chinese, English, French,

Regulatory approvals: EPEAT, CE, UL/cUL, CB,

GOST, C-Tick, RoHS, FCC, Class B

Miscellaneous

lapanese

Specifications

Connectivity

- Audio output: Audio Left/Right (RCA), External speaker connector
- Video input: DVI-D, VGA (Analog D-Sub), USB, Component (BNC), Composite (BNC), DisplayPort (1.2), HDMI (x2)
- Audio input: 3.5 mm jack, Audio Left/Right (RCA)
- Other connections: OPS, USB
- Video output: DisplayPort, DVI-I, VGA (via DVI-D)
- External control: RS232C (in/out) 2.5 mm jack, IR (in/out) 3.5 mm jack, RJ45

Picture/Display

- Diagonal screen size (metric): 163.9 cm
- Diagonal screen size (inch): 65 inch
- Aspect ratio: 16:9
- Panel resolution: 1920x1080p
- Pixel pitch: 0.74 x 0.74 mm
- Optimum resolution: 1920 x 1080 @ 60 Hz
- Brightness: 350 cd/m²
- Display colors: 1.07 Billion
- Contrast ratio (typical): 3000:1
- Dynamic contrast ratio: 500,000:1
- Response time (typical): 8 ms
- Viewing angle (horizontal): 178 degree
- · Viewing angle (vertical): 178 degree
- Picture enhancement: 3/2 2/2 motion pull down, 3D Combfilter, Motion compens. deinterlacing, Progressive scan, 3D MA deinterlacing, Dynamic contrast enhancement
- · Panel technology: VA

Convenience

- Placement: Landscape
- Tiled Matrix: Up to 10 x 15
- Screen saving functions: Pixel Shift, Low Brightness
- · Keyboard control: Hidden, Lockable
- Remote control signal: Lockable
- Signal loop through: DisplayPort, DVI, VGA, RS232
- · Ease of installation: Smart Insert
- Energy saving functions: Smart Power
- Network controllable: LAN (RJ45), RS232, One Wire (HDMI-CEC)

Sound

Built-in speakers: 2 x 10W RMS

Power

• Mains power: 100 ~ 240 VAC, 50 ~ 60 Hz

- Consumption (On mode): 176 W
- Standby power consumption: <0.5W
- Power Saving Features: Smart Power

Supported Display Resolution

- Computer formats: 640 x 480, 60, 67, 72, 75Hz, 1024 x 768, 60Hz, 1280 x 768, 60Hz, 1280 x 800, 60Hz, 1360 x 768, 60Hz, 1600 x 1200, 60Hz, 1920 x 1080, 60Hz, 1920 x 1200, 60Hz, 1280 x 1024, 60Hz, 720 x 400, 70Hz, 800 x 600, 60, 72, 75Hz
- Video formats: 480p, 60Hz, 576p, 50Hz, 720p, 50, 60Hz, 1080p, 50, 60Hz, 1080i, 25, 30Hz, 480i, 30, 60Hz, 576i, 25, 50Hz

Dimensions

- Smart Insert mount: 100×100 mm, 100×200 mm
- Set Width: 1458.7 mm
- Product weight: 24.8 kg
- Set Height: 834.7 mm
- Set Depth: 81.6 mm
- Set Width (inch): 57.43 inch
- Set Height (inch): 32.86 inch
- Wall Mount: 400 x 400 mm, M6
- Set Depth (inch): 3.21 inch
- Bezel width: 13.9 (Top/Left/Right) 14.9 (Bottom) mm
- Product weight (lb): 54.7 lb

Operating conditions


- Altitude: 0 ~ 3000 m
- Temperature range (operation): 0 \sim 40 $^{\circ}$ C
- MTBF: 50,000 hour(s)
- Relative humidity: 20 ~ 80 %
- Temperature range (storage): -20 ~ 60 °C


Multimedia Applications

- USB Playback Video: M2TS, M4V, MK3D, MKV, MP4, MPEG, MPG, MTS, TS, TTS, VOB, WMV
- USB Playback Picture: BMP, GIF, JPEG, JPG
- USB Playback Audio: AAC, AIF, AIFF, ASF, M4A, LPCM, M3U, MP3, MP4, WAV, WMA

Accessories

- Included accessories: AC Power Cord, RS232 cable, Remote Control, Batteries for remote control, User manual on CD-ROM, Quick start guide
- Optional accessories: Table top stand







Issue date 2024-03-23

Version: 5.1.1

© 2024 Koninklijke Philips N.V. All Rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

EAN: 87 12581 73977 5 ww

www.philips.com