

PHILIPS

Car signaling bulb

Ultinon LED

7443ALED-AMBER

Number of bulbs: 2

12 V, amber intense

Experience more light



7443AULAX2



Bright signaling. Stylish driving.

Durable LED quality

For a stylish drive, benefit from signaling lights with intense colors. Philips 7443ALED for turn signaling are bright, vibrant amber and look good so you can signal in safety and with style.

Stylish look

- Signal your intent with LED exterior lighting
- Intense amber turn signals to be seen better

Brighter LED exterior lights

- Upgrade your lights, upgrade your style

Long lasting LED lights

- Instant-on Performance
- Good light distribution for enhanced visibility

Good light diffusion

- Philips automotive lighting at the highest quality level

Durable Philips quality

- Easy installation and compatible with many car models
- Durable and long-lasting LED lighting

Highlights

Stylish exterior light

While the main goal of exterior lighting is to help you see and be seen, there's no reason why you shouldn't look good at the same time. If you're looking to upgrade your style, without buying a newer car, replacing your exterior lighting with LEDs is a smart way to spend your money. Upgrade your exterior lighting with a more intense red for stop lights, a vibrant amber for turning signals and bright white light for positioning and reversing. Your car is an expression of who you are, so make a style statement with Philips exterior signaling LED lights.

Stylish signaling colors

Signaling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. Bright signaling lights ensures you are seen for improved safety. Whether it's reversing, turning, or stopping, Philips Ultinon LED signaling lights provide you with the performance you need, giving other drivers vital extra time to react to your movements.

Vibrant amber turn signals

Philips LED turn signals feature vibrant amber color performance that make your intentions clear to surrounding traffic. Amber intense means more safety for you and others around you.

Good light diffusion

Philips LED exterior lighting range is designed for a smarter light distribution to ensure that exterior signaling light is projected where you need it (whether that's reversing, stopping, or signaling). With wide

angle and good light diffusion, not only can you see more of the road, other drivers can see more of you.

Automotive grade quality

The technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. The Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful bright light, and precise beam performance. You get high-end style.

Ready, steady, installed!

Designed to be easily installed in compatible vehicles, drivers with maintenance experience will be able to upgrade compatible lights with ease.

Long-lasting LED lighting

You want bright and stylish car lights. But you don't want to keep replacing failed lamps. That is a major weakness of conventional lights: the more powerful the light, the shorter its lifespan. At the same light intensity, LEDs last longer. And Philips Ultinon LED lights have additional resistance to heat and vibration, making them a perfect choice for long-lasting performance, with a lifetime of up to 8 years.

Excellent Light Distribution

The bright output and intense color adds more than just style. They provide superior light distribution, with a wide angle beam on the road so you can see and be seen better.

Specifications

Packaging Data

EAN1: 46678721489
EAN3: 50046678721484
Packaging type: X2

Product description

Technology: LED
Application: Side indicator
Range: Ultinon LED
Type: W21/5
Homologation ECE: NO
Base: W3x16q
Designation LED Type: 7443ALED-AMBER
Technical features: Instant-on

Electrical characteristics

Voltage: 12 V

Marketing specifications

Expected benefits: Experience more light
Product highlight: Bright signaling, Stylish Drive

Light characteristics

Color temperature: Amber intense

Ordering information

Order entry: 7443AULAX2
Ordering code: 78721484

Outerpack information

Gross weight per piece [lbs]: 1.17
Height [in]: 3.54
Length [in]: 7.87
Width [in]: 5.91

Packed product information

MOQ (for professionals): 10
Pack Quantity: 2
Gross weight per piece [lbs]: 0.03
Height [in]: 3.54
Length [in]: 2.76
Width [in]: 1.18

Lifetime

Life time: Up to 8 years

