



Philips Signage Solutions
Interactive whiteboard

75"

Powered by Android
Multi-touch

SignageSolutions

75BDL3151T

Engage them

10-point Multi-Touch display.

Inspire collaboration. Deliver information. This responsive Philips Multi-Touch Professional 4K UHD Display is ideal for multi-finger, multi-user applications-from wayfinding to presentations. Up to 10 touch points can be active at once.

Superb picture. Responsive touchscreen.

- 4K UHD. Rich, deep images. Stunning contrast
- Plug-and-play 10-point Multi-Touch display
- Android SoC processor. Native and web apps
- Interactive whiteboard app

Effortless setup. Total control.

- CMND & Deploy. Install and launch apps remotely
- Operate, monitor and maintain with CMND & Control
- CMND & Create. Develop and launch your own content

Versatile system solution

- Energy-saving automatic backlight control
- OPS slot allows for PC embedding without cabling
- Internal memory. Upload content for instant play

PHILIPS

Highlights

Powered by Android

Control your display via an Internet connection. Android-powered Philips Professional Displays are optimized for native Android apps, and you can install web apps directly to the display too. A built-in scheduler makes it easy to launch apps and content based on time of day.

CMND & Deploy

Quickly install and launch any app—even when you're off-site and working remotely. CMND & Deploy lets you add and update your own apps, as well as apps from the Philips Professional Display App Store. Simply scan the QR code, log in to the store, and click on the app you want to install. The app is automatically downloaded and launched.

CMND & Control



Run your display network over a local (LAN) connection. CMND & Control allows you to perform vital functions like controlling inputs and monitoring display status. Whether you're in charge of one screen or 100.


CMND & Create



Take control of your content with CMND & Create. A drag-and-drop interface makes it simple to publish your own content—whether it's a daily specials board or branded corporate information. Preloaded templates and

integrated widgets ensure your stills, text, and video will be up and running in no time.

OPS slot



Integrate a full-power PC or Android-powered CRD50 module directly into your Philips Professional Display. The OPS slot contains all the connections you need to run your slot-in solution, including a power supply.

Internal memory

Save and play content without the need for a permanent external player. Your Philips professional display has an internal memory, which allows you to upload media into the display for instant playback. The internal memory also functions as a cache for online streaming.

Specifications

Picture/Display

- Diagonal screen size: 74.5 inch / 189.3 cm
- Panel resolution: 3840 x 2160
- Optimum resolution: 3840 x 2160 @ 60Hz
- Brightness: 490 cd/m²
- Contrast ratio (typical): 1200:1
- Dynamic contrast ratio: 500,000:1
- Surface treatment: Anti-Glare coating
- Aspect ratio: 16:9
- Response time (typical): 8 ms
- Pixel pitch: 0.429 x 0.429 mm
- Display colors: 1.07Billion
- Viewing angle (H / V): 178 / 178 degree
- Picture enhancement: 3/2 - 2/2 motion pull down, 3D Combfilter, Motion compens. deinterlacing, Progressive scan, 3D MA deinterlacing, Dynamic contrast enhancement
- Panel technology: IPS

Interactivity

- Multi-touch technology: Infrared touch
- Touch points: 10 simultaneous touch points
- Plug and play: HID compliant
- Protection glass: 5 mm tempered safety glass, Anti-Glare, Anti-Reflective

Connectivity

- Video input: Composite (RCA), HDMI, HDMI (x4), VGA(Analog D-Sub) x2
- Video output: HDMI, VGA (Analog D-Sub)
- Audio input: Audio Left/Right (RCA), 3.5mm jack (x2), 3.5 mm jack
- Audio output: SPDIF
- Other connections: OPS, USB power outlet (5 V, 2 amp), USB(Type A) X4, USB(Type B) X2

Supported Display Resolution

• Computer formats

| Resolution | Refresh rate |
|-------------|--------------|
| 1024 x 768 | 60, 75Hz |
| 1280 x 1024 | 60Hz |
| 1280 x 768 | 60Hz |
| 1280 x 800 | 60Hz |
| 1360 x 768 | 60Hz |
| 1600 x 1200 | 60Hz |
| 1920 x 1080 | 60Hz |
| 3840 x 2160 | 60Hz |
| 640 x 480 | 60, 72, 75Hz |
| 720 x 400 | 70Hz |
| 800 x 600 | 60, 75Hz |

• Video formats

| Resolution | Refresh rate |
|------------|--------------|
| 1080p | 50, 60Hz |
| 1080i | 25, 30Hz |
| 480i | 30, 60Hz |
| 576i | 25, 50Hz |
| 720p | 50, 60Hz |
| 2160p | 30,50, 60Hz |
| 480p | 30, 60Hz |
| 576p | 25, 50Hz |

Convenience

- Placement: Landscape (18/7)

- Signal Loop Through: IR Loopthrough
- Network controllable: RS232, RJ45
- Picture performance: Advanced color control
- Screen saving functions: Pixel Shift, Low Brightness
- Keyboard control: Hidden, Lockable
- Remote control signal: Lockable
- Energy saving functions: Smart Power
- Other convenience: Carrying handles
- Ease of installation: Smart Insert
- Memory: 8GB eMMC

Dimensions

- Bezel width: 21.7 mm
- Set dimensions (W x H x D): 1739.7 x 1072.8 x 99.0 mm
- Set dimensions in inch (W x H x D): 68.49 x 42.24 x 3.90 inch
- VESA Mount: 400(H)x400(V), M8
- Product weight: 64.7 kg
- Product weight (lb): 142.64 lb
- Smart Insert mount: 100 x 200 mm

Sound

- Built-in speakers: 2 x 15W RMS

Operating conditions

- Temperature range (operation): 0 ~ 40 °C
- Relative humidity: 20 ~ 80%(Operational), 10 - 90%(Storage) %
- MTBF: 50,000 hour(s)
- Altitude: 0 ~ 3000 m
- Temperature range (storage): -20 ~ 60 °C

Power

- Mains power: 100 ~ 240 VAC, 50/60Hz
- Standby power consumption: <0.5W
- Consumption (Typical): 350 W
- Power Saving Features: Smart Power

Accessories

- Included accessories: AC Power Cord, RS232 cable, USB cable, Remote Control, Batteries for remote control, Quick start guide, HDMI cable, VGA cable
- Included Accessories: OPS Android player(CRD50)

Miscellaneous

- On-Screen Display Languages: Arabic, English, French, German, Italian, Japanese, Polish, Spanish, Turkish, Russian, Simplified Chinese, Traditional Chinese, Portuguese
- Regulatory approvals: CE, BSMI, CB, EPA, FCC, Class B
- Warranty: 3 year warranty

Multimedia Applications

- USB Playback Audio: AAC, M4A, MP3, WMA
- USB Playback Picture: BMP, JPEG, JPG, PNG
- USB Playback Video: 3GP, ASF, AVI, DAT, FLV, MKV, MOV, MP4, MPG, TS, VOB, WMV3



Issue date 2020-08-31

Version: 6.0.1

12 NC: 8670 001 45507
EAN: 87 12581 74635 3

© 2020 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com