




Philips Signage Solutions
Q-Line Display

75"

Direct LED Backlight
Ultra HD

SignageSolutions



75BDL3510Q

Stand out

Easy-setup 18/7 display.

Inform and enthrall with a Philips Q-Line Professional Ultra HD Display. This reliable solution can be up and running as quickly as you need.

Effortless setup. Total control.

- Operate, monitor and maintain with CMND & Control
- OPS slot allows for PC embedding without cabling
- Schedule what you want, when you want with SmartPlayer

Cost-effective system solution

- Energy-saving automatic backlight control
- Integrated media player. Easily schedule USB content
- Easy control. Remotely manage networked displays
- FailOver ensures content is always playing

Superb picture. Ultra-high brightness.

- Ultra-HD. Rich images. Stunning contrast

PHILIPS

Highlights

CMND & Control




Run your display network over a local (LAN) connection. CMND & Control allows you to perform vital functions like controlling inputs and monitoring display status. Whether you're in charge of one screen or 100.

Integrated media player

Easily schedule content to play from USB. Your Philips Professional Display will wake from standby to play the content you want, and then return to standby once playback is done.

FailOver



From waiting room to meeting room, never show a blank screen. FailOver lets your Philips Professional Display switch automatically between primary and secondary inputs ensuring content keeps playing even if the primary source goes down. Simply set a list of alternate inputs to be sure your business is always on.


SmartPlayer



Turn your USB into a true cost effective digital signage device. Simply save your content

(video, audio, pictures) on your USB and plug into your display. Create your playlist and schedule your content via the on screen menu, and enjoy your own created playlists anytime, anywhere.

OPS slot



Integrate a full-power PC or Android-powered CRD50 module directly into your Philips Professional Display. The OPS slot contains all the connections you need to run your slot-in solution, including a power supply.

Specifications

Picture/Display

- Diagonal screen size: 74.5 inch / 189.3 cm
- Panel resolution: 3840 x 2160
- Optimum resolution: 3840 x 2160 @ 60 Hz
- Brightness: 400 cd/m²
- Contrast ratio (typical): 1200:1
- Dynamic contrast ratio: 500,000:1
- Response time (typical): 8 ms
- Aspect ratio: 16:9
- Viewing angle (H / V): 178 / 178 degree
- Pixel pitch: 0.4296 x 0.4296 mm
- Display colors: 1.07 Billion
- Picture enhancement: 3/2 - 2/2 motion pull down, 3D Combfilter, Motion compens. deinterlacing, Progressive scan, 3D MA deinterlacing, Dynamic contrast enhancement
- Panel technology: ADS
- Clinical image: D-Image preset (dicom part 14 compatible)

Supported Display Resolution

• Computer formats

| Resolution | Refresh rate |
|-------------|------------------|
| 1920 x 1080 | 60Hz |
| 1680 x 1050 | 60Hz |
| 1600 x 1200 | 60Hz |
| 1440 x 900 | 60Hz |
| 1280 x 1024 | 60Hz |
| 1280 x 800 | 60Hz |
| 1280 x 720 | 60Hz |
| 1152 x 870 | 75Hz |
| 1024 x 768 | 60, 70, 75Hz |
| 800 x 600 | 56, 60, 72, 75Hz |
| 720 x 400 | 70Hz |
| 640 x 480 | 60, 67, 72, 75Hz |
| 1152 x 864 | 75Hz |
| 832 x 624 | 75Hz |

• Video formats

| Resolution | Refresh rate |
|-------------|--------------|
| 3840 x 2160 | 60Hz |
| 3840 x 2160 | 30Hz |
| 720p | 60Hz |
| 576p | 50Hz |
| 576i | 50Hz |
| 480p | 60Hz |
| 480i | 60Hz |
| 1080i | 50, 60Hz |
| 1080p | 50, 60Hz |

Connectivity

- Video input: DVI-I (x 1), HDMI 2.0 (x3), USB 2.0 (x2)
- Audio input: 3.5 mm jack
- Audio output: 3.5mm jack
- External control: RS232C (in/out) 2.5 mm jack, IR (in/out) 3.5 mm jack, RJ45
- Other connections: OPS

Convenience

- Keyboard control: Hidden, Lockable
- Network controllable: RS232, RJ45
- Signal loop through: RS232, IR Loopthrough
- Energy saving functions: Smart Power
- Remote control signal: Lockable
- Tiled Matrix: Up to 15 x 15
- Placement: Landscape, Portrait
- Start-up: Switch on delay, Switch on status, Boot on source
- Start-up window: enable / disable Philips logo
- Ease of installation: Smart Insert

Dimensions

- Bezel width: 14.9 mm (Even bezel)
- Set dimensions (W x H x D): 1683.5 x 961.7 x 69.5mm(D@wall mount) / 91.8mm(D@handle) mm
- Set dimensions in inch (W x H x D): 66.28 x 37.86 x 2.74(@ wall mount)/ 3.61(@ handle) inch
- Product weight: 37.5 kg
- Product weight (lb): 82.67 lb
- VESA Mount: 600 x 400 mm, M8

Operating conditions

- Altitude: 0 ~ 3000 m
- Temperature range (operation): 0 ~ 40 °C
- Temperature range (storage): -20 ~ 60 °C
- MTBF: 50,000 hour(s)
- Humidity range (operation)[RH]: 20 ~ 80% RH (No condensation)
- Humidity range (storage) [RH]: 5 ~ 95% RH (No condensation)

Power

- Mains power: 100 - 240V~, 50/60Hz
- Standby power consumption: <0.5W
- Power Saving Features: Smart Power
- Consumption (Max): 305 W

- Consumption (Typical): 150 W
- Energy Label Class: G

Sound

- Built-in speakers: 2 x 10W RMS

Accessories

- Included accessories: AC Power Cord, RS232 cable, Remote Control, Batteries for remote control, Quick start guide
- Included Accessories: IR sensor cable (1.8 m) (x1), RS232 daisy-chain cable, HDMI cable (1.8 m) (x1), M3 screw (X1), Philips logo (x1), USB Cover (x1)


Multimedia Applications

- USB Playback Video: MPEG, H.264, JPEG, WMV3
- USB Playback Picture: BMP, JPEG, PNG
- USB Playback Audio: AAC, WMA, HEAAC, MPEG

Miscellaneous

- Warranty: 3 year warranty
- On-Screen Display Languages: Simplified Chinese, Traditional Chinese, English, French, German, Italian, Polish, Spanish, Turkish, Japanese, Arabic, Russian
- Regulatory approvals: CE, CB, BSMI, CU, EPA, ETL, FCC, Class A, VCCI

Philips 75BD3510Q
Version: 3.0
Release Date: 2020/03/17



Issue date 2021-05-26

Version: 3.0.1

12 NC: 8670 001 66093
EAN: 87 12581 76526 2

© 2021 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com