

Preliminary

Philips  
Recessed spot light

80083 4" 8W 27K Silver

silver  
LED

80083/27/66



## Essential lighting for a bright home

Complete your home in style with the Philips Essalu LED downlight Silver. Made of high quality diecast aluminum, it is accented with decorative ring and incorporates long lasting LED light source and high quality anti glare diffuser.

### **Premium quality**

- Die-casted aluminum for a premium look and feel

### **Energy saving**

- Built-in LED, as part of the system

### **Light effect**

- Even light distribution

### **Long lifespan**

- Extremely long life 20,000 hours

**PHILIPS**

# Preliminary

Recessed spot light  
80083 4" 8W 27K Silver silver, LED

## Specifications

### Design and finishing

- Material: aluminium
- Color: silver

### Extra feature/accessory incl.

- LED integrated
- Diffused light effect
- Resistant high quality material
- Photometric data available
- Protection sleeve included

### Product dimensions & weight

- Length: 13.9 cm
- Width: 7.7 cm
- Net weight: 0.219 kg
- Recessed distance: 8.0 cm
- Cut out length: 12.5 cm
- Cut out width: 12.5 cm

### Technical specifications

- Mains power: Range 100 V - 240 V, 50-60 Hz
- Bulb technology: LED, 230 V
- Number of bulbs: 32

- Wattage bulb included: 0.5 W
- Maximum wattage replacement bulb: 0.5 W
- Light color: warm white
- Fixture dimmable: No
- LED
- Built in LED
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II - double insulated

### Service

- Warranty: 1 year(s)

### Packaging dimensions & weight

- Height: 14.8 cm
- Length: 14.3 cm
- Width: 8.5 cm
- Weight: 0.273 kg

### Miscellaneous

- Especially designed for: Living- & Bedroom
- Style: Functional
- Type: Recessed spot light

800832766

## Highlights

### Premium materials



Die-casted aluminum for a premium look and feel

### Integrated LED light source



A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

### Even light distribution



Even light distribution

### Extremely long life



A light source you can trust. Philips LED lights offer an extremely long-life of at least 20,000 hours (which equals 20 years on basis of an average use of 3 hours / day with an amount of at least of 13,000 on/off switching cycles). It feels so comfortable to think that you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.



Issue date 2017-11-11  
Owner: Yonglan Yi  
Version: 1.0.1

12 NC: 9150 048 92301  
EAN: 69 47830 42552 5

Test leaflet, for internal use only!  
© 2017 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)