



Philips Ultinon HID  
Headlight bulb

D2S  
85V  
35W

85122FSX2

## Double the light/more varieties for unique needs

The Ultinon HID bulb is a High Intensity Discharge bulb filled with a mixture of special salts and gases including Xenon.

### For instant upgrade and replacement

- 200% brighter than standard bulbs
- 50% less energy consumption than halogen bulbs
- 2,500 hour lifespan almost equal to car life
- UV-blocking quartz glass

# PHILIPS

Headlight bulb  
D2S 85V, 35W

# Specifications

## Technical specifications

- Base: P32d-2
- Description: D2S 6700K
- Range: FS

- Voltage: 85 V
- Wattage: 35 W

## Packaging Data

- Packing: X2

85122FSX2

# Highlights

## 200% brighter than standard bu

200% brighter than standard bulbs

## 50% less energy consumption th

50% less energy consumption than halogen bulbs

## 2,500 hour lifespan almost equ

2,500 hour lifespan almost equal to car life

## UV-blocking quartz glass

UV-blocking quartz glass



Issue date 2018-07-24

Version: 5.0.1

12 NC: 8670 001 00202

© 2018 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding  
B.V. or their respective owners.

[www.philips.com](http://www.philips.com)