



Philips Ultinon HID
Headlight bulb

D2S
85V
35W

85122FSX2

Double the light/more varieties for unique needs

The Ultinon HID bulb is a High Intensity Discharge bulb filled with a mixture of special salts and gases including Xenon.

For instant upgrade and replacement

- 200% brighter than standard bulbs
- 50% less energy consumption than halogen bulbs
- 2,500 hour lifespan almost equal to car life
- UV-blocking quartz glass

PHILIPS

Headlight bulb
D2S 85V, 35W

Specifications

Technical specifications

- Base: P32d-2
- Description: D2S 6700K
- Range: FS

- Voltage: 85 V
- Wattage: 35 W

Packaging Data

- Packing: X2

85122FSX2

Highlights

200% brighter than standard bu

200% brighter than standard bulbs

50% less energy consumption th

50% less energy consumption than halogen bulbs

2,500 hour lifespan almost equ

2,500 hour lifespan almost equal to car life

UV-blocking quartz glass

UV-blocking quartz glass



Issue date 2018-06-19

Version: 5.0.1

12 NC: 8670 001 00202

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding
B.V. or their respective owners.

www.philips.com