


Preliminary



Philips Xenon X-tremeVision plus
Xenon car headlight bulb

Type of lamp: D2S

Pack of: 2
85 V, 35 W
More light



85122XV2X2

Feel safe and drive safe with brighter lights

See every bump, curve and obstacle in the road

With a powerful beam that pushes light emission to the limit, X-tremeVision plus is the latest development in Xenon technology. This outstanding light performance extends your driving limits, so you enjoy a safer, more comfortable drive.

Brighter for maximum visibility and safety

- Xenon X-tremeVision plus: for superior visual performance

Light spectrum: a comfortable driving experience

- Better visibility for safer, more comfortable driving

Optimal light performance

- Directing the light to the right spot in front of your car
- Philips car lamps are award-winning
- Respecting high quality standards of the ECE homologation

Xenon quality and ultra resistant car lamp

- Philips invented innovative Xenon HID technology

Original equipment, 100% road legal

- Philips is the choice of major car manufacturers.
- Philips car lamps are made of high-quality quartz glass
- Philips car lamps are protected from UV damage

PHILIPS

焦點

Up to 150% more vision

Xenon X-tremeVision plus lamps are engineered with Philips Xenon technology for ultimate performance. Producing a longer beam and up to 150% more vision, X-tremeVision plus lamps help you spot obstacles earlier, allowing you to react in time. And with improved peripheral vision, you'll have greater awareness of any dangers at the side of the road, such as pedestrians or upcoming junctions. Brightly illuminating every bump, curve and hazard in the road, these are headlamps to satisfy the most demanding drivers and the most demanding driving conditions.

Maximum safety and visibility

Light is a fundamental part of the driving experience. Simply by improving the quality of light you can help prevent accidents. The Xenon X-tremeVision gen 2 improves visibility, so you're able to recognize obstacles and traffic signs earlier, improving your reaction times. The spectral composition of this light is adapted to the natural color sensitivity of your eye. And with 4800K color temperature, this headlamp produces light that's gentle on your eyes, making the night-time driving experience safer and more comfortable.

Optimal light performance

It's not enough to just have powerful headlights; optical precision matters, too. The Xenon X-tremeVision plus lamps have the most precise arc bending technology aligned at 150-350µm. This means they illuminate the road just where you need it, without dazzling oncoming drivers.

Award-winning car lamps

Our high-quality and innovative vehicle lights are award-winning, being consistently recognized by automotive experts.

Car manufacturers' choice

For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become

standards on modern automobiles. Today, one in two cars in Europe and one in three worldwide, is equipped with Philips lighting.

ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

High quality quartz glass

UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. So Philips quartz-glass lamps are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light. And more powerful light means an enhanced driving experience, how ever dark the road in front of you.

Original Xenon technology

Xenon HID (High Intensity Discharge) lamps offer twice as much light for safer driving in all conditions. Studies have shown xenon automotive lighting helps drivers to concentrate on the road and to distinguish obstacles and road signs much faster than with traditional lamps. And what better way to defeat darkness than with an intense white light comparable to daylight?

UV resistant glass

Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions. This additional protective layer ensures your headlamps are built to last.

規格

Packaging Data

- Packaging type: X2
- EAN1: 8727900377675
- EAN3: 8727900377682

Electrical characteristics

- Voltage: 85 V
- Wattage: 35 W

Lifetime

- Life time: B3/Tc = 1500/2500

Light characteristics

- Color temperature: up to 4800k
- Lumens: 3200 ± 450

Ordering information

- Order entry: 85122XV2X2
- Ordering code: 37763794

Outerpack information

- Height: 14.5 cm
- Length: 32.1 cm
- Width: 12 cm
- Gross weight per piece: 1.126 kg
- Net weight per piece: 179 g

Product description

- Type: D2S
- Application: High beam, Low beam
- Designation: D2S X-tremeVision plus
- Homologation ECE: YES
- Range: X-tremeVision Plus
- Technology: Xenon
- Base: P32d-2

Packed product information

- Pack Quantity / MOQ: 2
- Gross weight per piece: 112.6 g
- Height: 12.8 cm
- Length: 11.2 cm
- MOQ (for professionals): 5
- Net weight per piece: 17.94 g
- Width: 6.2 cm

Marketing specifications

- Expected benefits: Safety
- Product highlight: Experience more light



發行日期 2018-06-17
Owner: Marilyn Denis
版本 : 5.0.1

12 NC: 8670 001 42762

Test leaflet, for internal use only!
© 2018 Philips Lighting Holding B.V.
所有權利均予保留。

規格若有變更恕不另行通知。商標為 Philips Lighting Holding B.V. 或其個別所有者的財產。

www.philips.com