



Philips Ultinon HID 6000K  
Headlight bulb

Type of lamp: D2R

Pack of: 2  
85 V,35 W

85126WXX2



## Drive with style

Instant upgrade to 6000K flash white light

Philips Ultinon HID (WX) is a 6000K white light Xenon HID bulb that enhances your style on the road

### 6000K flash white light for more style on the road

- Ultinon HID (WX) is the upgrade for your Xenon headlight

### Maximum safety with Xenon HID

- Powerful light from Xenon HID bulb offers maximum safety

### Original equipment manufacturer

- Philips is the choice of major car manufacturers
- Philips car lamps are made of high-quality quartz glass
- Philips car lamps are highly resistant against humidity
- Philips car lamps are highly UV resistant

# PHILIPS

Headlight bulb  
Type of lamp: D2R Pack of: 2, 85 V,35 W

# Highlights

## 6000K Flash white upgrade

Philips Ultinon HID (WX) lamps are designed for drivers who want a stunning styling effect for their cars. The 6000K brilliant white light makes the car truly stunning compared to others.

## Maximum safety with Xenon HID

Xenon HID (High Intensity Discharge) lamps offer twice as much light\* for safer driving in all conditions. The intense white light produced by the Xenon HID lamps is comparable to daylight. Studies have demonstrated that xenon automotive lighting helps drivers to concentrate on the road and to distinguish obstacles and road signs much faster than traditional lamps. \*compared to standard halogen bulbs

## Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

## High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light

## Resistance against humidity

Only a burning bulb made of quartz glass (filament 2650°c, glass 800°c) can resist thermal shocks : such as, if a drop of cold water touches the hot bulb, when you drive through water with a broken headlight unit.

## UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensures their longevity

85126WXX2

# Specifications

## Packaging Data

- Packing: X2
- EAN1: 8727900373462
- EAN3: 8727900373479

## Electrical characteristics

- Voltage: 85 V
- Wattage: 35 W

## Lifetime

- Life time: B3/Tc = 1000/1500

## Light characteristics

- Color temperature: 5800 K
- Light output: 2100 ±250 lumen

## Marketing specifications

- Expected benefits: Whiter light
- Product highlight: 6000K

## Outerpack information

- Gross weight per piece: 1,15 kg
- Height: 14 cm
- Length: 35 cm
- Width: 17,5 cm

## Packed product information

- Gross weight per piece: 108 g
- Height: 7 cm
- Length: 12,5 cm
- Net weight per piece: 20,64 g
- Pack Quantity / MOQ: 10
- Width: 16 cm

## Product description

- Application: High beam, Low beam
- Base: P32d-3
- Homologation ECE: NO
- Marking ECE: N/A
- Range: Ultinon HID - WX, Ultinon HID (WX), Ultinon HID 6000K
- Technology: Xenon
- Designation: D2R WX
- Type: D2R

## Ordering information

- Ordering code: 37346228



Issue date 2020-02-03

Version: 11.0.1

12 NC: 8670 001 18824

© 2020 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)

\* Application varies per bulb type