

PHILIPS

Headlight bulb

X-tremeVision

Type of lamp: D2R

Pack of: 1

85 V,35 W



85126XVS1



Feel safe, drive safe

Up to 50% more vision

Producing up to 50% more vision, this high-power xenon lighting solution provides maximum brightness for maximum visibility to satisfy the needs of the most demanding drivers. Philips Xenon X-tremeVision is the ultimate choice for drivers.

Brighter light for maximum visibility and safety

- Better visibility for safer driving
- Xenon X-treme vision is the ultimate performance solution

Xenon quality and ultra resistant car lamp

- Philips is the inventor of Xenon HID technology
- Philips car lamps are highly UV resistant
- Philips car lamps are made of high-quality quartz glass
- Philips car lamps are highly resistant against humidity

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Award winning car lamp manufacturer
- Respecting high quality standards of the ECE homologation

Highlights

Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

Rewarded Car lamps



Our lamps are often rewarded by automotive experts

Maximum safety and visibility

Xenon X-treme Vision provides you with a better reactivity thanks to an earlier recognition of obstacles and traffic signs. Light is a fundamental part of the driving experience and light is the first and only part of the safety circle that actually helps prevent accidents. Philips promotes active safety protection to prevent accidents by increasing overall visibility and road illumination as a matter of fact the 4800K color temperature increases the visual confort.

Original Xenon technology



Xenon HID (High Intensity Discharge) lamps offer twice as much light for safer driving in all conditions. As a matter of fact, the intense white light produced by the Xenon HID lamps is comparable to daylight. Studies have demonstrated that xenon automotive lighting helps drivers to concentrate on the road and to distinguish obstacles and road signs much faster than traditional lamps.

Up to 50% more vision

Xenon X-tremeVision lamps are engineered with Philips Xenon technology for ultimate performance. Producing a longer beam, Xenon X-treme vision helps you to see obstacles earlier and improves the side perception. By producing even more light, Xenon X-treme vision lamps stasify the most

demanding drivers while maintaining its high Original Equipment quality and superior performance.

UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensures their longevity

High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light.

Resistance against humidity

Only a burning bulb made of quartz glass can resist thermal shocks : if a drop of cold water touches the hot bulb, which can happen when you drive through water with a broken headlight unit.

Specifications

Packaging Data

EAN3: 8727900364651

EAN1: 8727900364644

Packaging type: S1

Electrical characteristics

Voltage: 85 V

Wattage: 35 W

Lifetime

Life time: 2500h

Light characteristics

Color temperature: 4700 K

Lumens: 2800 ±450 lm

Ordering information

Order entry: 85126XVS1

Ordering code: 36464433

Outerpack information

Gross weight per piece: 0.2 kg

Height: 14 cm

Length: 14.6 cm

Width: 13.1 cm

Product description

Type: D2R

Application: High beam, Low beam

Designation: D2R X-tremeVision

Homologation ECE

Range: X-tremeVision

Technology: Xenon

Base: P32d-3

Packed product information

Pack Quantity: 1

MOQ (for professionals): 2

Gross weight per piece: 100.5 g

Height: 14 cm

Length: 12.5 cm

Net weight per piece: 18.1 g

Width: 6.8 cm

Marketing specifications

Expected benefits: More light

Product highlight: Up to 50% more light

