

Philips
Ultinon HID

D1S
85V 35W

85410WXX2



Double the light/more varieties for unique needs

The Ultinon HID bulb is a High Intensity Discharge bulb filled with a mixture of special salts and gases including Xenon.

For instant upgrade and replacement

- 200% brighter than standard bulbs
- 50% less energy consumption than halogen bulbs
- 2,500 hour lifespan almost equal to car life
- UV-blocking quartz glass

PHILIPS
sense and simplicity

Ultinon HID
D1S 85V 35W

Specifications

Technical specifications

- Base: PK32d-2
- Description: D1S 6000K
- Range: WX

- Voltage: 85 V
- Wattage: 35 W

Packaging Data

- Packing: X2

85410WXX2

Highlights

200% brighter than standard bu

200% brighter than standard bulbs

50% less energy consumption th

50% less energy consumption than halogen bulbs

2,500 hour lifespan almost equ

2,500 hour lifespan almost equal to car life

UV-blocking quartz glass

UV-blocking quartz glass



Issue date 2013-01-31

Version: 1.0.1

12 NC: 8670 001 01357

© 2013 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com