

# PHILIPS

Headlight bulb

Ultinon HID

Type of lamp: D1S

Pack of: 2

85 V, 35 W

85410WXX2



## Double the light/more varieties for unique needs

The Ultinon HID bulb is a High Intensity Discharge bulb filled with a mixture of special salts and gases including Xenon.

### 6000K flash white light for more style on the road

- Ultinon HID (WX) is the upgrade for your Xenon headlight

### Maximum safety with Xenon HID

- Powerful light from Xenon HID bulb offers maximum safety

### Original equipment manufacturer

- Philips is the choice of major car manufacturers
- Philips car lamps are made of high-quality quartz glass
- Philips car lamps are highly resistant against humidity
- Philips car lamps are highly UV resistant

# Highlights

## 6000K Flash white upgrade

Philips Ultinon HID (WX) lamps are designed for drivers who want a stunning styling effect for their cars. The 6000K brilliant white light makes the car truly stunning compared to others.

## Maximum safety with Xenon HID

Xenon HID (High Intensity Discharge) lamps offer twice as much light\* for safer driving in all conditions. The intense white light produced by the Xenon HID lamps is comparable to daylight. Studies have demonstrated that xenon automotive lighting helps drivers to concentrate on the road and to distinguish obstacles and road signs much faster than traditional lamps. \*compared to standard halogen bulbs

## Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

## High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light

## Resistance against humidity

Only a burning bulb made of quartz glass (filament 2650°C, glass 800°C) can resist thermal shocks : such as, if a drop of cold water touches the hot bulb, when you drive through water with a broken headlight unit.

## UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensures their longevity

# Specifications

## Technical specifications

Base: PK32d-2

Description: D1S 6000K

Range: WX

Voltage: 85 V

Wattage: 35 W

## Packaging Data

Packing: X2

EAN1: 8727900373288

EAN3: 8727900373295

## Lifetime

Life time: B3/Tc = 800/1500

## Light characteristics

Lumens: 2300 lm

## Marketing specifications

Product highlight: 6000K

## Ordering information

Ordering code: 37328828

Order entry: 85410WXX2

## Product description

Range: Ultinon HID - WX, Ultinon HID

