



Philips Ultinon HID
Headlight bulb

Type of lamp: D1S

Pack of: 2
85 V,35 W

85410WXX2



Double the light/more varieties for unique needs

The Ultinon HID bulb is a High Intensity Discharge bulb filled with a mixture of special salts and gases including Xenon.

6000K flash white light for more style on the road

- Ultinon HID (WX) is the upgrade for your Xenon headlight

Maximum safety with Xenon HID

- Powerful light from Xenon HID bulb offers maximum safety

Original equipment manufacturer

- Philips is the choice of major car manufacturers
- Philips car lamps are made of high-quality quartz glass
- Philips car lamps are highly resistant against humidity
- Philips car lamps are highly UV resistant

PHILIPS

Headlight bulb
Type of lamp: D1S Pack of: 2, 85 V,35 W

Highlights

6000K Flash white upgrade

Philips Ultinon HID (WX) lamps are designed for drivers who want a stunning styling effect for their cars. The 6000K brilliant white light makes the car truly stunning compared to others.

Maximum safety with Xenon HID

Xenon HID (High Intensity Discharge) lamps offer twice as much light* for safer driving in all conditions. The intense white light produced by the Xenon HID lamps is comparable to daylight. Studies have demonstrated that xenon automotive lighting helps drivers to concentrate on the road and to distinguish obstacles and road signs much faster than traditional lamps. *compared to standard halogen bulbs

Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light

Resistance against humidity

Only a burning bulb made of quartz glass (filament 2650°c, glass 800°c) can resist thermal shocks : such as, if a drop of cold water touches the hot bulb, when you drive through water with a broken headlight unit.

UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensures their longevity

85410WXX2

Specifications

Technical specifications

- Base: PK32d-2
- Description: D1S 6000K
- Range: WX
- Voltage: 85 V
- Wattage: 35 W

Packaging Data

- Packing: X2
- EAN1: 8727900373288
- EAN3: 8727900373295

Lifetime

- Life time: B3/Tc = 800/1500

Light characteristics

- Lumens: 2300 lm

Marketing specifications

- Product highlight: 6000K

Ordering information

- Ordering code: 37328828
- Order entry: 85410WXX2

Product description

- Range: Ultinon HID - WX, Ultinon HID



Issue date 2020-02-03

Version: 9.0.1

12 NC: 8670 001 01357

© 2020 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com