

# PHILIPS

Xenon car headlight  
bulb

Xenon Vision

Type of lamp: D1S

Pack of: 1

85 V, 35 W



85415VIC1



## Feel safe, drive safe

### Ideal for replacement

Philips Xenon Vision replaces a single burned-out lamp while matching the colour of the unchanged one thanks to its new single-lamp replacement technology. Therefore it is the ideal replacement lamp and it's economical too!

#### **The point of reference for xenon bulb replacement**

- Replace one by one
- Xenon Vision perfectly matches the unchanged Xenon lamp

#### **Xenon quality and ultra-resistant car bulb**

- Philips is the inventor of Xenon HID technology
- Philips car lamps are highly UV resistant

#### **Original Equipment manufacturer**

- Philips is the choice of major car manufacturers
- Award-winning car lamp manufacturer
- Complying with the high quality standards of ECE homologation

# Highlights

## Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

## ECE homologation

Philips automotive products and services are considered best in class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high-quality products and tested to the highest specifications, our products are designed to maximise the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

## Award-winning car lamps



Our lamps are often rewarded by automotive experts

## Economical choice

Thanks to its single lamp replacement technology Xenon Vision allows you to change your bulbs one by one while matching the

colour temperature of the unchanged lamp. It is the most economical choice for lamp replacement.

## Original Xenon technology



Xenon HID (High Intensity Discharge) lamps offer twice as much light for safer driving in all conditions. As a matter of fact, the intense white light produced by the Xenon HID lamps is comparable to daylight. Studies have demonstrated that xenon automotive lighting helps drivers to concentrate on the road and to distinguish obstacles and road signs much faster than traditional lamps.

## Single-lamp replacement

Philips Xenon Vision replaces a single burnt-out lamp while matching the colour of the unchanged one. Its new single-lamp replacement technology allows for one-by-one replacement while still matching the colour temperature of the unchanged lamp. Thus, Xenon Vision is the perfect solution for single-lamp replacement.

## UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensuring their longevity

# Specifications

## Packaging Data

EAN3: 8727900364743  
EAN1: 8727900364736  
Packaging type: C1

## Electrical characteristics

Voltage: 85 V  
Wattage: 35 W

## Lifetime

Life time: Up to 2500 h

## Light characteristics

Lumens: 3350 ±300 lm  
Colour temperature: Up to 4300 K

## Ordering information

Order entry: 85415VIC1  
Ordering code: 36473633

## Outer pack information

Height: 5.7 cm  
Length: 11.1 cm  
Width: 9.6 cm  
Gross weight per piece: 0.204 kg

## Product description

Type: D1S  
Application: High beam, Low beam  
Designation: D1S Vision  
Homologation ECE  
Range: Xenon Vision  
Technology: Xenon  
Base: PK32d-2

## Packed product information

Pack Quantity: 1  
MOQ (for professionals): 2  
Gross weight per piece: 97 g  
Height: 9.3 cm  
Length: 5.4 cm  
Net weight per piece: 73.2 g  
Width: 5.4 cm

## Marketing specifications

Expected benefits: More light  
Product highlight: Ideal for replacement

