

PHILIPS

Headlight bulb

Xenon X-tremeVision gen2

Type of lamp: D1S

Pack of: 1

85 V,35 W



85415XV2S1



Feel safe and drive safe with brighter lights See every bump, curve and obstacle in the road

With a powerful beam that pushes light emission to the limit, X-tremeVision gen2 is the latest development in xenon technology. This outstanding light performance extends your driving limits, so you enjoy a safer, more comfortable drive.

Brighter for maximum visibility and safety

- Xenon X-tremeVision gen2: for superior visual performance

Light spectrum: a comfortable driving experience

- Better visibility for safer, more comfortable driving

Optimal light performance

- Directing the light to the right spot in front of your car

Xenon quality and ultra resistant car lamp

- Philips invented innovative Xenon HID technology

Original equipment manufacturer

- Philips car lamps are made of high-quality quartz glass
- Protection from UV damage
- The favored choice of all major car manufacturers
- Philips car lamps are award-winning
- Respecting high quality standards of the ECE homologation

Highlights

Up to 150% more vision

Xenon X-tremeVision gen2 lamps are engineered with Philips Xenon technology for ultimate performance. Producing a longer beam and up to 150% more vision, X-tremeVision gen2 lamps help you spot obstacles earlier, allowing you to react in time. And with improved peripheral vision, you'll have greater awareness of any dangers at the side of the road, such as pedestrians or upcoming junctions. Brightly illuminating every bump, curve and hazard in the road, these are headlamps to satisfy the most demanding drivers and the most demanding driving conditions.

Maximum safety and visibility

Light is a fundamental part of the driving experience. Simply by improving the quality of light you can help prevent accidents. The Xenon X-tremeVision gen 2 improves visibility, so you're able to recognize obstacles and traffic signs earlier, improving your reaction times. The spectral composition of this light is adapted to the natural color sensitivity of your eye. And with 4800K color temperature, this headlamp produces light that's gentle on your eyes, making the night-time driving experience safer and more comfortable.

Optimal light performance

It's not enough to just have powerful headlights; optical precision matters, too. The Xenon X-tremeVision gen2 lamps have the most precise arc bending technology aligned

at 150–350µm. This means they illuminate the road just where you need it, without dazzling oncoming drivers.

Original Xenon technology

Xenon HID (High Intensity Discharge) lamps offer twice as much light for safer driving in all conditions. Studies have shown xenon automotive lighting helps drivers to concentrate on the road and to distinguish obstacles and road signs much faster than with traditional lamps. And what better way to defeat darkness than with an intense white light comparable to daylight?

High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. So Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light. And more powerful light means an enhanced driving experience, how ever dark the road in front of you.

UV resistant glass

Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions. This additional protective layer ensures your lights are built to last.

Chosen by car manufacturers

For over 100 years, Philips lamps have been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard in modern vehicles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

Award-winning car lamps

Our high-quality and innovative vehicle lights are award-winning, being consistently recognized by automotive experts.

ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

Specifications

Packaging Data

Packaging type: S1
EAN1: 8727900376975
EAN3: 8727900376982

Electrical characteristics

Voltage: 85 V
Wattage: 35 W

Lifetime

Life time: 2500h

Light characteristics

Lumens: 3200 ±450 lm
Color temperature: Up to 4800 K

Ordering information

Order entry: 85415XV2S1
Ordering code: 37697533

Outerpack information

Height: 14 cm
Length: 15 cm
Width: 13 cm

Product description

Type: D1S
Application: High beam, Low beam
Designation: D1S X-tremeVision
Homologation ECE

Range: Xenon X-tremeVision gen2

Technology: Xenon

Base: PK32d-2

Packed product information

Gross weight per piece: 136 g
Height: 14 cm
Length: 13 cm
MOQ (for professionals): 2
Pack Quantity: 1
Width: 7 cm

Marketing specifications

Expected benefits: More light
Product highlight: Experience more light

