



Philips X-tremeVision  
Headlight bulb

Type of lamp: D1S

Pack of: 1  
85 V,35 W



85415XVS1

## Feel safe, drive safe

Up to 50% more vision

Producing up to 50% more vision, this high-power xenon lighting solution provides maximum brightness for maximum visibility to satisfy the needs of the most demanding drivers. Philips Xenon X-tremeVision is the ultimate choice for drivers.

### Brighter light for maximum visibility and safety

- Better visibility for safer driving
- Xenon X-treme vision is the ultimate performance solution

### Xenon quality and ultra resistant car lamp

- Philips is the inventor of Xenon HID technology
- Philips car lamps are highly UV resistant
- Philips car lamps are made of high-quality quartz glass
- Philips car lamps are highly resistant against humidity

### Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Award winning car lamp manufacturer
- Respecting high quality standards of the ECE homologation

# PHILIPS

Headlight bulb  
Type of lamp: D1S Pack of: 1, 85 V,35 W

# Highlights

## Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

## ECE homologation

Philips automotive products and services are considered best-in-class in the Original Equipment Manufacturer market and the aftermarket. Manufactured from high quality products and tested to the highest specifications, our products are designed to maximize the safety and comfort of our customers' driving experience. Our entire product range is thoroughly tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements. Put simply, this is quality you can trust.

## Rewarded Car lamps



Our lamps are often rewarded by automotive experts

## Maximum safety and visibility

Xenon X-treme Vision provides you with a better reactivity thanks to an earlier recognition of obstacles and traffic signs. Light is a fundamental part of the driving experience and light is the first and only part of the safety circle that actually helps prevent accidents. Philips promotes active safety protection to prevent accidents by increasing overall visibility and road illumination as a matter of fact the 4800K color temperature increases the visual confort.

## Original Xenon technology



Xenon HID (High Intensity Discharge) lamps offer twice as much light for safer driving in all conditions. As a matter of fact, the intense white light produced by the Xenon HID lamps is comparable to daylight. Studies have demonstrated that xenon automotive lighting helps drivers to concentrate on the road and to distinguish obstacles and road signs much faster than traditional lamps.

## Up to 50% more vision

Xenon X-tremeVision lamps are engineered with Philips Xenon technology for ultimate performance. Producing a longer beam, Xenon X-treme vision helps you to see obstacles earlier and improves the side perception. By producing even more light, Xenon X-treme vision lamps satisfy the most demanding drivers while maintaining its high Original Equipment quality and superior performance.

85415XVS1

## UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensures their longevity

## High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light.

## Resistance against humidity

Only a burning bulb made of quartz glass can resist thermal shocks : if a drop of cold water touches the hot bulb, which can happen when you drive through water with a broken headlight unit.

Headlight bulb  
Type of lamp: D1S Pack of: 1, 85 V,35 W

85415XVS1

# Specifications

## Packaging Data

- EAN3: 8727900364613
- EAN1: 8727900364583
- Packaging type: S1

## Electrical characteristics

- Voltage: 85 V
- Wattage: 35 W

## Lifetime

- Life time: 2500h

## Light characteristics

- Color temperature: 4800±600 K
- Lumens: 3200 ±450 lm

## Ordering information

- Order entry: 85415XVS1
- Ordering code: 36458333

## Outerpack information

- Gross weight per piece: 0.305 kg
- Height: 14 cm

- Length: 14.6 cm
- Width: 13.1 cm

## Product description

- Type: D1S
- Application: High beam, Low beam
- Designation: D1S X-tremeVision
- Homologation ECE
- Range: X-tremeVision
- Technology: Xenon
- Base: PK32d-2

## Packed product information

- Pack Quantity: 1
- MOQ (for professionals): 2
- Gross weight per piece: 152.5 g
- Height: 14 cm
- Length: 12.5 cm
- Net weight per piece: 73.2 g
- Width: 6.8 cm

## Marketing specifications

- Expected benefits: More light
- Product highlight: Up to 50% more light



Issue date 2020-02-03

Version: 6.0.1

12 NC: 9285 156 29405  
EAN: 87 27900 36458 3

© 2020 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)