

Philips
Xenon HID conversion kit

H1
12V
35W

858094KX2



Easy fit for better sight

The Philips Xenon HID conversion kit is your chance to convert from standard halogen headlamps to the brightest and whitest Xenon bulbs.

Xenon HID Bulb - Genuine Philips quality

- Original HID bulbs
- Superior beam pattern
- Comprehensive product available for almost all car models

Ballast - Easy Installation

- Intergrated ballast with starter
- Complete installation kit

PHILIPS

Xenon HID conversion kit
H1 12V, 35W

Specifications

Technical specifications

- Base: P14,5s
- Description: Conv. bulb H1
- Range: 4K

- Voltage: 12 V
- Wattage: 35 W

Packaging Data

- Packing: X2

858094KX2

Highlights

Original HID bulbs

Original HID bulbs

Superior beam pattern

3-axis alignment

Comprehensive product

Comprehensive product available for almost all car models

Integrated ballast

Integrated ballast with starter

Complete installation kit

Everything included to upgrade your car lighting (in connection with Philips Xenon HID bulb)



Issue date 2016-12-21

Version: 3.0.1

12 NC: 8670 000 97941

© 2016 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com