



Philips
Xenon HID conversion kit

Conv. Bulb H4 H/LB
12V
35W

858166KX2

Easy fit for better sight

The Philips Xenon HID conversion kit is your chance to convert from standard halogen headlamps to the brightest and whitest Xenon bulbs.

Xenon HID Bulb - Genuine Philips quality

- Original HID bulbs
- Superior beam pattern
- Comprehensive product available for almost all car models

Ballast - Easy Installation

- Intergrated ballast with starter

PHILIPS

Xenon HID conversion kit
Conv. Bulb H4 H/LB 12V, 35W

858166KX2

Specifications

Technical specifications

- Base: P43t-38
- Description: Conv. bulb H4 H/LB
- Range: 6K

- Voltage: 12 V
- Wattage: 35 W

Packaging Data

- Packing: X2

Highlights

Original HID bulbs

Original HID bulbs

Superior beam pattern

3-axis alignment

Comprehensive product

Comprehensive product available for almost all car models

Integrated ballast

Integrated ballast with starter



Issue date 2016-12-22

Version: 2.0.1

12 NC: 8670 001 01428

© 2016 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com