



Philips Signage Solutions
Multi-Touch Display

86"

Powered by Android
500cd/m²

SignageSolutions

86BDL4152T

Chasing innovation

powered by Android

Amaze your guests with a smarter, faster, signage display. With integrated WiFi, designed for running Android apps, and multiple touch points, it's the next evolution in signage solutions.

Innovative solutions for any signage application

- Android: Run your own app or choose your favorite app to run
- Enhance your connectivity with an integrated mPCIe slot.
- Integrated WiFi
- Save and play content with internal memory
- Android: Run your own app or choose your favorite app to run

Maximizing the impact of your message

- CMND: Take control of your displays
- Create and update content with CMND & Create
- Manage settings of multiple displays with CMND & Control
- Connect and control your content via the cloud

Care about you, your business and your audience

- Ensure your content is running with automatic screenshots
- Keep your content up and running with FailOver
- Simplify meetings with FailOver for conferencing

PHILIPS

Highlights

Powered by Android

With Android OS integrated into the display, you can work with the most developed OS on the planet and save your own app directly into the display. Or, choose from the large library of Android apps and play content from there. With the built-in scheduler, you can daypart your apps and content based on your customer and time of day and with the auto orientation feature, showing content in portrait or landscape is as simple as turning the display.

PCI Slot

With an integrated PCI slot, you can connect a WiFi/bluetooth or 4G LTE module, allowing for even greater communication with the display. Machine to machine communication is also enhanced, with numerous configurations available for customers to use, such as the ability to expand product features or signal-handling capability.

Proof of Play

Content is king, and with the automatic screenshot feature, you can make sure that your content is up and running at all times. Screenshots are taken throughout the day, which are then stored in the FTP server. From there, the screenshots can be viewed no matter when, or where you are.

FailOver



Keeping your content up and running is critical for demanding commercial applications. While it is unlikely you will face a content disaster, FailOver provides content protection with a revolutionary technology that plays back-up

content on screen in the event of a media player failure. FailOver automatically kicks in when the primary input fails. Simply select a primary input connection and a FailOver connection and your ready for instant protection.

FailOver for Meeting Rooms


Using FailOver, simplify your presentations and videoconferencing. When a meeting or conference room is not in use, background content can run from whatever input source you choose. When the meeting starts and you need to share a presentation or your screen, simply connect your computer and the display automatically switches inputs and shows what's on your screen, with no need to manually switch inputs.

SmartPower



The backlight intensity can be controlled and pre-set by the system to reduce the power consumption by up to 50%, which saves substantially on energy costs.

CMND



A robust display management platform, CMND puts the power back into your hands. Update and manage content with CMND & Create or control your settings with CMND & Control. It's all possible with CMND.

CMND & Control



With CMND & Control, easily manage multiple displays in a central location. With real time display monitoring, setting and software updates from a remote location, and the ability to customize and configure multiple displays at once, such as video wall or menu board displays, controlling your suite of displays has never been easier.

CMND & Create



Design and create compelling content with CMND & Create, a powerful authoring tool. With a drag and drop interface, preloaded templates, and integrated widgets, you'll be able to amaze your customers with compelling content. Available in portrait and landscape mode.

SmartBrowser



Connect and control your content via the cloud with the integrated HTML5 browser. Using the Chromium based browser, design your content online and connect a single display, or your complete network. Show content in both landscape and portrait mode, with fullHD resolution. Streaming content can also be shown in a PIP (picture-in-picture) window. Simply connect the display to the internet using WiFi or with an RJ45 cable, and enjoy your own created playlists

Specifications

Picture/Display

- Diagonal screen size: 85.6 inch / 217.42 cm
- Panel resolution: 3840 x 2160
- Optimum resolution: 3840x 2160 @ 60Hz
- Brightness: 500 cd/m²
- Contrast ratio (typical): 1200
- Dynamic contrast ratio: 500,000:1
- Aspect ratio: 16:9
- Response time (typical): 12 ms
- Pixel pitch: 0.4935 (H) x 0.4935 (V)
- Display colors: 1.07 billion
- Viewing angle (H / V): 178 / 178 degree
- Picture enhancement: 3/2 - 2/2 motion pull down, 3D Combfilter, Motion compens. deinterlacing, 3D MA deinterlacing, Dynamic contrast enhancement, Progressive scan

Connectivity

- Video input: DisplayPort, DVI-D (x1), VGA (Analog D-Sub)
- Video output: DisplayPort
- Audio input: 3.5 mm jack
- Audio output: 3.5mm jack, SPDIF
- Other connections: mPCIe, micro SD, micro USB, USB power outlet (5 V, 2 amp), OPS
- External control: RJ45, RS232C (in/out) 2.5 mm jack, IR (in/out) 3.5 mm jack

Supported Display Resolution

• Video formats

| Resolution | Refresh rate |
|------------|--------------|
| 480p | 60Hz |
| 480i | 60Hz |
| 1080i | 50Hz |
| 1080i | 60Hz |
| 1080p | 50, 60Hz |
| 4K x 2K | |
| 576i | 50Hz |
| 576p | 50Hz |
| 720p | 60Hz |

• Computer formats

| Resolution | Refresh rate |
|-------------|------------------|
| 1024 x 768 | 60, 75Hz |
| 1024x768 | 60,70Hz |
| 1152 x 864 | 60, 70, 75Hz |
| 1152 x 900 | 66Hz |
| 1280 x 720 | 60,70Hz |
| 1280 x 768 | 60Hz, 75Hz |
| 1280 x 800 | 60,75Hz |
| 1280 x 960 | 60Hz |
| 1280x1024 | 60,67,75Hz |
| 1360 x 768 | 60Hz |
| 1366 x 768 | 60Hz |
| 1400 x 1050 | 60, 75Hz |
| 1440 x 1050 | 60Hz |
| 1440 x 900 | 60, 75Hz |
| 1600 x 1200 | 60Hz |
| 1600 x 900 | 60Hz |
| 1680 x 1050 | 60Hz |
| 1920 x 1080 | 60Hz |
| 1920 x 1200 | 60Hz |
| 640 x 350 | 70Hz |
| 640 x 480 | 60, 67, 72, 75Hz |
| 720 x 400 | 70Hz |
| 800 x 600 | 56, 60, 72, 75Hz |
| 832 x 624 | 75Hz |
| 848 x 480 | 60Hz |
| 960 x 720 | 60,75Hz |
| 960x720 | 75Hz |

Dimensions

- Set dimensions (W x H x D): 1957 x 1128 x 104.9 mm
- Set dimensions in inch (W x H x D): 77.05 x 44.4 x 4.13 inch
- Bezel width: 9.5 (T/L/R) 15.6 (B)
- Product weight (lb): 212.1 lb
- Product weight: 96.21 kg
- VESA Mount: 600(H)x400(V) mm, M8
- Smart Insert mount: 100 x 100 mm, 100 x 200 mm

Convenience

- Placement: Landscape, Portrait
- Tiled Matrix: Up to 15 x 15
- Keyboard control: Hidden, Lockable
- Signal loop through: RS232, IR Loopthrough
- Network controllable: RJ45, RS232, One Wire (HDMI-CEC), HDMI (One Wire)
- Energy saving functions: Smart Power
- Screen saving functions: Pixel Shift, Low Bright

- Ease of installation: Smart Insert
- Picture in picture: PIP

Power

- Standby power consumption: <0.5 W
- Mains power: 100 ~ 240 VAC, 50 ~ 60 Hz
- Consumption (Typical): 262 W
- Consumption (Max): 450 W

Operating conditions

- Temperature range (operation): 0 ~ 40 °C
- Temperature range (storage): -20 ~ 60 °C
- Relative humidity: 20 ~ 80 %
- Altitude: 0 ~ 3000 m
- MTBF: 50,000 hour(s)

Sound

- Built-in speakers: 2 x 10W RMS

Accessories

- Included accessories: Quick start guide, RS232 cable, AC Power Cord, IR sensor cable (1.8M), Remote Control & AAA Batteries
- Stand: BMO5922 (Optional)
- Optional accessories: ColourCalibrationKit (CCK4602)
- Included Accessories: IR sensor cable (1.8 m), M2 screw (x3), M3 screw (x1), Philips logo, RS232 Daisy chain cable (1.8m, SD card cover (x1), Wifi dipole antenna (x2)

Multimedia Applications

- USB Playback Audio: AAC, M4A, MP3, WMA
- USB Playback Picture: BMP, JPEG, JPG, PDF
- USB Playback Video: MKV, MP4, MPEG, MPG, TS, VOB, WMV, ASF, AVI, FLV, WEBM

Miscellaneous

- On-Screen Display Languages: English, French, German, Spanish, Polish, Turkish, Russian, Italian, Simplified Chinese, Traditional Chinese, Arabic, Japanese, Danish, Dutch, Finnish, Norwegian, Portuguese, Swedish
- Regulatory approvals: EnergyStar 7.0, CE, FCC, Class B, UL/cUL, CCC, C-Tick, RoHS, GOST, BSMI, CB, J-Moss, PSE, VCCI
- Warranty: 3 year warranty

Internal Player

- CPU: Dual-Core Cortex-A72 @2GHz, Quad-Core Cortex-A53 @ 1.5GHz
- GPU: ARM Mali-T860 MP4
- Memory: 4GB RAM
- Storage: 64G eMMC

Multi-touch Interactivity

- Touch points: 10 simultaneous touch points



Issue date 2020-11-04

Version: 4.1.1

12 NC: 8670 001 56368
EAN: 87 12581 75355 9

© 2020 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com