



Philips LED
Spot

2 W (35 W)
GU10 cap
White



8718291664307



Durable accent lighting with a focused bright beam

Avoid the hassle of changing spots

Philips LED spots provide an exceptionally long life and significant energy savings. With its bright color temperature, this spot is the perfect long-lasting replacement for your modern lighting spots.

Create an active atmosphere

- Cool, energizing light (3000K)
- High color rendering (CRI > 80) for vivid colors

Pure and elegant design

- Smooth surface and high-quality finishing

Easy to enjoy

- Avoid the hassle of constant changing

Sustainable choice

- Lasts up to 10 years
- Very low energy consumption, saving up to 90%



PHILIPS

Spot
2 W (35 W) GU10 cap, White

Highlights

Cool, energizing light (3000K)

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more cozy light, while those with a higher Kelvin value produce a cool, more energizing light.

Avoid hassle of changing bulbs



The durable alternative to halogen spots, Philips LED spots can be installed and forgotten about, maintaining their beautiful light beam for years and years to come.

High color rendering (CRI>80)



The color rendering index (CRI) is used to describe the effect of a light source on color appearance. Natural outdoor light has a CRI of 100 and is used as the standard of comparison for any other light source. The CRI of Philips LED light bulbs is always

higher than 80, close to the sun's value, reflecting colors truly and naturally.

Very low energy consumption



By replacing traditional light bulbs with a Philips LED alternative, you will gain immediate, significant energy savings while contributing to a sustainable planet.

Lasts up to 10 years



With a lifetime of up to 10,000 hours, this Philips LED lamp will ensure your desired atmosphere for up to 10 years.*

Smooth surface

Designed to last, this LED spot offers all of the most recent innovations based in high-quality materials. It is a truly perfect fit for your current fixtures.

8718291664307

Specifications

Bulb characteristics

- Shape: Spot
- Cap/fitting: GU10
- Voltage: 220-240 V
- Dimmable: No

Power consumption

- Wattage: 2 W
- Wattage equivalent: 35 W
- Energy efficiency label: A+
- Power consumption per 1000h: 2 kW h

Light characteristics

- Light output: 130 lumen
- Application: Accent light
- Beam angle: 50 degree
- Color: White
- Color temperature: 3000 K
- Light effect/finish: White
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color consistency: 6 SDCM
- Rated center beam intensity: 120 cd
- Color rendering index (CRI): 80

Durability

- Lifetime of lamp: 10000 hour(s)
- Number of switch cycles: 50000
- Lumen maintenance factor: 0.7
- Average life (at 3 hrs/day): 10 year(s)

Bulb dimensions

- Height: 55 mm
- Width: 50 mm

Other characteristics

- Mercury content: 0 mg
- Power factor: 0.5
- Lamp current: 45 mA

Rated values

- Rated power: 2.0 W
- Rated luminous flux: 130 lumen
- Rated lifetime: 10000 hour(s)
- Rated beam angle: 50 degree



Issue date 2017-10-25

Version: 4.0.2

12 NC: 9290 002 46201
EAN: 87 18291 66430 7

© 2017 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

*Based on average usage of 3 hours per day