

Philips Hue White
ambiance
Starter kit E27

2 x E27 bulb

Bridge included
Dimmer switch included
Shades of white (2200-6500K)



8718696548752

Light for your moments

From sunrise to sunset

Philips Hue white ambiance can help you to fall asleep and wake up gently. It can energize you and help you to concentrate, read and relax. Set the right ambiance with a range of white light, from cool daylight to relaxing warm white light.

Light for your moments

- Wake up and go to sleep naturally
- Create your ambiance with warm white to cool daylight
- Relax, read, concentrate and energize with light recipes
- Relax
- Read
- Concentrate
- Energize

Easy control and comfort

- Smart control, home and away
- Set timers for your convenience
- Installation free dimming
- Control it your way
- Hue dimmer switch included




PHILIPS

Starter kit E27
2 x E27 bulb Bridge included, Dimmer switch included, Shades of white (2200-6500K)

8718696548752

Highlights

Wake up and go to sleep



Philips Hue will help get you out of bed the way you like it, helping you start your day feeling refreshed. The light brightness increases gradually mimicking the effect of sunrise and helps you wake up naturally, instead of being woken up by the loud sound of an alarm clock. Start your day, the right way. In the evening, the relaxing warm white light helps you to unwind, relax and prepare your body for a good night's sleep.

Create your ambiance



Set the right ambiance for any moment and decorate your home with warm to cool white light. Enjoy different styles throughout the year, no matter if it's the crisp white light reminding you of a spring breeze, the warm white light of a summer sun, or the ice cool daylight of winter.

Light for your daily routines



Light influences our mood and behavior. Philips Hue can help you to customize your daily routines into moments you can enjoy. Skip your morning coffee and get ready for the day with cool, bright white daylight that helps to energize your body and mind. Stay focussed with finely tuned bright white light. Or put your feet up and relax with a soft glow of white light for the perfect end of the day.

Relax




Put your feet up and relax with the soft glow of white light for the perfect end of the day. Relaxing white light can help you to unwind in the evening and sleep better at night

Read




Get lost in your favorite book for hours on end with Philips Hue. It provides you with the right white light for a perfect read

Concentrate



Stay focused with finely tuned bright white light. It can help you get things done quickly and efficiently without distractions, whether you're studying for an exam, working from home, or choosing the perfect outfit to look your best

Energize



Skip your morning coffee and get ready for the day with cool, bright white daylight that helps to energize your body and mind. Perfect for those moments when your batteries are running low and you need a kickstart

Specifications

The bulb

- Fitting: E27
- Wattage equivalent: 60 W
- Power factor: >0.5
- Number of switching cycles: 50000
- Energy efficiency label: A+
- Rated lifetime: 25000 hour(s)
- Form factor: A19
- Lifetime: 25000 hour(s)
- Color temperature: 2200K-6500K
- Wattage: 9.5 W
- Input voltage: 220V-240V
- Light output: From warm to cold white color, >80 CRI @ 4000K, Dimmable via smart device only
- Lumen output: 806 lm
- Software upgradable
- Start up: Instant 100% light output
- Height: 110 mm
- Height: 4.3 inch
- Max. operation power: 9.5 W
- Max. standby power: 0.1 W

The bridge

- Height: 3.5 X 3.5 inch
- Height: 88 X 88 mm
- Frequency band: 2400~2483.5 MHz
- Max. number of accessories: 12
- Max. number of bulbs: 50
- Mounting options: Wall
- Power adapter: 100~240 V AC / 50~60Hz

The switch

- Batteries included: 1 x CR2450
- Configurable buttons: 1
- Max Tap switches per bridge: 25 if no other switches linked
- Max. lights per switch: 10 if not linked to Hue bridge
- Range: 15-30m
- Minimal battery lifetime: 3 year(s)

- Minimal range indoor: 500 inch
- Minimal range outdoor: 13 m
- Mounting options: freestanding
- Switch depth: 11 mm
- Switch height: 117 mm
- Switch width: 35 mm
- Wall plate depth: 114 mm
- Wall plate height: 14 mm
- Wall plate width: 70 mm
- Weight including wall plate: 67 g

What's in the box

- Bridge
- Ethernet network cable
- Power adapter
- Hue bulbs
- Tone bulbs: 2

Environmental

- Operational humidity: 5% < H < 95% (non condensing)
- Operational temperature: 0°C - 40°C

Guarantee

- 2 years

What's supported

- IOS
- HomeKit compatible
- iPad
- iPhone

Also tested on

- Android
- Google Nexus
- HTC
- Motorola Nexus
- Note
- Samsung Galaxy



Issue date 2018-04-02

Version: 9.0.1

12 NC: 9290 012 00104
EAN: 87 18696 54875 2

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com