

Philips LED
Bulb

8W-5W-2W(60W)

E27
Warm/Very Warm/Extra Warm
Non-dimmable

8718696588840



One bulb three light settings

Works with your existing switch

Sometimes you feel like a change in ambiance to suit whatever you're doing. With a Philips SceneSwitch LED bulb, you can easily change the setting with your existing switch.

No dimmer or additional installation is required.

Choose for high quality light

- Learn about light

Light beyond illumination

- Three light settings from 2700 K to 2500 K to 2200 K
- No dimmer or additional installation needed
- The lamp can memorize your last setting
- Restore the lamp to the default factory setting

Choose a simple replacement for your old bulbs

- No UV or InfraRed

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years
- Better for your wallet and your planet

Comfortable LED light that is easy on your eyes

- Designed for the comfort of your eyes

PHILIPS

Highlights

Three light settings

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, cozy light, while those with a higher Kelvin value produce a more energizing light. These new Scene Switch bulbs allow you to switch from functional lighting to natural light and to a cozy, warm dimmed light. Light levels can change from 100% to 40% to 10%. Now you can easily customize your room for a variety of tasks or adapt it to suit your mood.

Plug and play



Delivers a variety of great light scenes straight out of the box to suit your different needs and moods. The intelligence is in the bulb itself, so no dimmer or other additional installation is required. Simply replace your bulb with this Scene Switch bulb, and you can change between different scenes at a flick of your existing wall switch. Lowest level of investment and effort required to enjoy the highest level of comfort. Now you can change the ambiance easily to suit whatever you're doing and your mood at the time.

Reset (Sceneswitch)



If multiple lamps are used and they are no longer synchronized, simply toggle the switch (turn it on and off again within 1 second) to restore the lamps to the default factory setting.

Auto memory (sceneswitch)




This Scene Switch lamp has a built-in memory chip which will memorize your last light setting if the switch is turned off for longer than 6 seconds. If you don't often switch between activities, the light will be in your favorite mode when you turn it on again.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Saves up to 80% energy



LED technology saves up to 80% energy compared to your standard bulb. It therefore pays for itself and saves you money year after year. It also helps protect the environment.

No UV or IR



The light has no infra-red component, so no heat is radiated. Also, there is no ultra-violet component in this light. These two characteristics mean that this light will not cause fabric and other items to fade.

Specifications

Bulb characteristics

- Cap/fitting: E27
- Dimmable: No
- Voltage: 220 - 240 V
- Wattage: 8-5-2
- Wattage equivalent: 60
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Technology: LED
- Type of glass: Frosted

Power consumption

- Energy efficiency label: A+
- Power consumption per 1000h: 8i kW h

Light characteristics

- Light output: 806-320-80 lumen
- Color: Warm/Very Warm/Extra Warm
- Color temperature: 2700-2500-2200 K
- Color rendering index (CRI): 80
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color consistency: 6 SDCM
- Suitable for accent lighting?

Durability

- Lifetime of lamp: 15000 hour(s)
- Number of switch cycles: 100000
- Lumen maintenance factor: 0.7
- Average life (at 2.7 hrs/day): 15 year(s)

Bulb dimensions

- Height: 111 mm
- Width: 61 mm
- Weight: 0.059 kg

Other characteristics

- Mercury content: 0 mg
- Power factor: 0.5
- Lamp current: 100 mA
- Range: SceneSwitch
- Efficacy: 100 K

Rated values

- Rated power: 8-5-2 W
- Rated luminous flux: 806-320-80 lumen
- Rated lifetime: 15000 hour(s)



Issue date 2018-10-02

Version: 8.1.1

12 NC: 9290 012 36558

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

* Designed for the comfort of your eyes. Visit www.philips.com/eyecomfort for flicker, strobe and other criteria and product details.