



Philips Hue  
Motion sensor

### Wireless installation

Battery powered  
Automates your lights  
Mounts anywhere



8718696595190

## Automatically switches lights

for your convenience

Trigger your smart lights with movement with the Hue motion sensor. The battery-powered sensor can be placed anywhere inside your home with hassle-free installation.

### Limitless possibilities

- Mount the motion sensor anywhere
- Daylight sensor detects light
- Customise motion sensor lights
- Trigger smart lights with motion sensors
- Requires a Philips Hue bridge



# PHILIPS

## Motion sensor

Wireless installation Battery powered, Automates your lights, Mounts anywhere

# Highlights

### Mount anywhere



The motion sensor for Philips Hue smart lights is battery powered and completely wireless, allowing you to install anywhere inside your home. Place it on a shelf, mount it on a wall or ceiling with a single screw, or place it on any magnetic surface with the included magnet.

### Daylight sensor



The Hue Motion sensor's integrated daylight sensor detects when there is still enough daylight so that lights do not turn on until you need them. If it's still too dark, adjust the light sensitivity of the sensor in the Philips Hue app to personalise when you'd like the motion sensor to activate.

### Customise motion sensor lights



With the Hue smart motion sensor, you can customise the lights that come on and their intensity

depending on the time of day. During the evening, set the motion sensor to trigger gentle night lights to guide you in the dark. During the day, trigger crisp white light to flood your halls.

### Trigger with motion sensor



Add a Philips Hue motion sensor to your smart lighting system to automatically switch your lights on when movement is detected, helping you navigate safely through your home.

### Requires a Philips Hue bridge



This product requires a connection to the Philips Hue bridge

8718696595190

# Specifications

### The switch

- IP rating: IP42
- Minimal battery lifetime: 2 year(s)
- Mounting options: freestanding
- Software upgradeable: when connected to Hue bridge
- Sensor depth: 20 mm
- Sensor height: 55 mm
- Sensor width: 55 mm
- Zigbee Light link: protocol IEEE 802.15.4

### What's in the box

- Bridge: No
- Ethernet network cable: No
- Power adapter: No
- Hue bulbs: No
- Hue dimmer switch: No
- Hue white bulbs: No

### Guarantee

- 2 years



Issue date 2018-12-28

Version: 7.2.1

12 NC: 9290 012 60701

© 2018 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)