


Philips LED
Spot

4.5W-2.8W-1.3W (50W)

GU10 cap
Warm white
Non-dimmable

8718696681459



One spot three light settings

Works with your existing switch

If you feel like a change in ambiance to suit whatever you're doing. Easily select your setting. Works with your existing light switch. No dimmer or additional installation needed.

Create a warm atmosphere

- Three light settings from 2700 K to 2500 K to 2200 K

Easy to enjoy

- No dimmer or additional installation needed
- Restore the lamp to the default factory setting

Innovative optical design

- The lamp can memorize your last setting

PHILIPS

Spot
4.5W-2.8W-1.3W (50W) GU10 cap, Warm white, Non-dimmable

8718696681459

Highlights

Auto memory (sceneswitch)



This Scene Switch lamp has a built-in memory chip which will memorize your last light setting if the switch is turned off for longer than 6 seconds. If you don't often switch between activities, the light will be in your favorite mode when you turn it on again.

Plug and play



Delivers a variety of great light scenes straight out of the box to suit your different needs and moods. The intelligence is in the bulb itself, so no dimmer or other additional installation is required. Simply

replace your bulb with this Scene Switch bulb, and you can change between different scenes at a flick of your existing wall switch. Lowest level of investment and effort required to enjoy the highest level of comfort. Now you can change the ambiance easily to suit whatever you're doing and your mood at the time.

Reset (Sceneswitch)



If multiple lamps are used and they are no longer synchronized, simply toggle the switch (turn it on and off again within 1 second) to restore the lamps to the default factory setting.

Three light settings

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, cozy light, while those with a higher Kelvin value produce a more energizing light. These new Scene Switch bulbs allow you to switch from functional lighting to natural light and to a cozy, warm dimmed light. Light levels can change from 100% to 40% to 10%. Now you can easily customize your room for a variety of tasks or adapt it to suit your mood.

Bulb characteristics

- Shape: Spot
- Cap/fitting: GU10
- Dimmable: No
- Voltage: 220 - 240 V

Power consumption

- Wattage: 4.5-2.8-1.3 W
- Wattage equivalent: 50 W
- Energy efficiency label: A+
- Power consumption per 1000h: 5 kW h

Light characteristics

- Light output: 385-150-45 lumen
- Beam angle: 36 degree
- Color temperature: 2700-2500-2200 K
- Light effect/finish: Warm White
- Color rendering index (CRI): 80
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color: Warm White

Durability

- Lifetime of lamp: 15000 hour(s)
- Number of switch cycles: 100000
- Lumen maintenance factor: 0.7
- Average life (at 2.7 hrs/day): 15 year(s)

Bulb dimensions

- Height: 55 mm
- Width: 50 mm

Other characteristics

- Mercury content: 0 mg
- Power factor: .45
- Lamp current: 40 mA

Rated values

- Rated power: 4.5-2.8-1.3 W
- Rated luminous flux: 385-150-45 lumen
- Rated lifetime: 15000 hour(s)
- Rated beam angle: 36 degree



Issue date 2017-10-26

Version: 1.0.1

12 NC: 9290 012 64319

© 2017 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com