




Philips DiamondVision
Headlight bulb

Type of lamp: Car

Pack of: 2
12 V, 27 W



881DVS2

Drive with style

5000K ultimate white light

Philips DiamondVision halogen headlamp is the ultimate style upgrade for your car with 5000K white light. With the specially designed blue coating, DiamondVision makes you stand out from the crowd. .

Stylish white light stands out

- Cool elegance for your headlights

High quality and ultra resistant headlamp

- Philips car lamps are made of high-quality quartz glass[^]
- Philips car lamps are highly resistant against humidity[^]
- Philips car lamps are highly UV resistant
- Wide range of 12V lamps for all functions
- Change both your headlamps simultaneously for more safety
- Philips is the choice of major car manufacturers.

PHILIPS

Headlight bulb
Type of lamp: Car Pack of: 2, 12 V,27 W

881DVS2

Specifications

Marketing specifications

- Expected benefits: Ultimate white light
- Product highlight: 5000K

Product description

- Technology: Halogen
- Application: Additional high beam, High beam, Low beam
- Base: PGJ13
- Range: DiamondVision
- Homologation ECE: NO
- Marking ECE: N/A
- Designation: 881
- Type: 881 DiamondVision

Electrical characteristics

- Voltage: 12 V
- Wattage: 55 W

Light characteristics

- Color temperature: up to 5000 K
- Lumens: 150 lm \pm 15 % lm

Lifetime

- Life time: 300 h

Ordering information

- Ordering code: 35252830

Packaging Data

- Packaging type: S2
- EAN1: 8727900352528
- EAN3: 8727900352535

Packed product information

- Gross weight per piece: 126,5 g
- Height: 10.9 cm
- Length: 10.9 cm
- Net weight per piece: 12,6 g
- Pack Quantity / MOQ: 20
- Width: 5.3 cm

Outerpack information

- Height: 12.6 cm
- Length: 27.6 cm
- Width: 22.8 cm
- Gross weight per piece: 2,53 kg



Issue date 2018-11-09

Version: 7.0.1

12 NC: 8670 001 19131

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

* Application varies per bulb type