

PHILIPS

upgrade headlight
bulb

CrystalVision ultra

Type of lamp: 9003

Pack of: 2

12 V,60/55 W

Style



9003CVB2



Bright white light

Drive with style

Philips CrystalVision ultra headlights provide a bright white light on the road using blue coating on the glass. The perfect choice for those who want to drive with style, without compromising on safety.

High quality upgrade headlight

- Upgrade headlights that enhance the style of your vehicle

Innovative automotive lighting solutions

- Philips is the choice of major car manufacturers

DOT Compliant

- Philips CrystalVision ultra headlights are DOT compliant

Replace in pairs

- Don't compromise on safety, change in pairs

Upgrade your ride with bright white light

- Halogen upgrade headlights with bright white light

Highlights

Enhance the style of your ride

CrystalVision ultra upgrade headlights enhance the style of your vehicle while offering improved performance compared to standard bulbs. Philips CrystalVision headlight bulbs ultra are an excellent choice if you want to add style to your vehicle, without compromising on safety.

Bright white light on the road

Philips CrystalVision ultra is for drivers who are looking for an upgrade with the style and performance. Without compromising on safety, Philips CrystalVision ultra headlights rival the look of HID thanks to the blue coating on the glass and the blue cap bulb which creates a bright white light effect in the headlamp's reflector in daytime.

Don't compromise on safety

Headlight bulbs put out less light as they age. That means that old bulb is giving you less nighttime visibility that you would have with 2 new bulbs. Putting in a new pair gives you

all the light you should be getting for maximum driving safety for you and your family.

Original equipment quality

Our lighting solutions produce a powerful and precise beam of light with maximum output. We consistently produce the best, most efficient lighting solutions because we know that our high-quality lighting may one day save a life. For over 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern cars. Today, one in three cars worldwide is equipped with a Philips light source.

Personalize your vehicle

With CrystalVision ultra upgrade headlight bulbs, drivers enjoy a look that is unmatched and a DOT compliant bulb.

Specifications

Product description

Technology: Halogen

Application: High beam, Low beam

Range: CrystalVision ultra

Base: P43t

DOT Compliant

Type of lamp: 9003

Electrical characteristics

Voltage: 12 V

Wattage: 60/55 W

Marketing specifications

Expected benefits: More style

Product highlight: Bright white light

Ordering information

Order entry: 9003CVB2

Packaging Data

Packaging type: B2

