



Philips MotoVision
Motorcycle headlight bulb

9003MVB1

Number of bulbs: 1
12 V
Up to 40% more vision*



9003MVB1

Maximum safety

Designed to increase driver visibility

With up to 40% more vision*, MotoVision delivers greater nighttime visibility and safety, allowing cyclists to see and be seen better. *Compared to standard minimum legal requirements in low beam headlamp test results.

Durable Philips quality

- Philips automotive lighting at the highest quality level
- Easy installation

Enhanced visibility

- See and be seen on the road

Ideal for off-road terrain

- Greater nighttime visibility

Unique orange reflection

- Maximum visibility

Vibration resistant, up to 10G

- State-of-the-art technology

PHILIPS

Specifications

Packaging Data

- Packaging type: B1
- EAN1: 046678722714

Product description

- Technology: Halogen
- Application: High beam, Low beam
- Base: P43t-38
- Designation: 9003 MotoVision
- Range: MotoVision
- Type: MotoVision
- Homologation ECE: NO
- Designation LED Type: 9003MVB1

Electrical characteristics

- Wattage: 60/55 W
- Voltage: 12 V

Marketing specifications

- Expected benefits: Up to 40% more vision*
- Product highlight: Unique orange reflection

Ordering information

- Order entry: 9003MVB1
- Ordering code: 78722719

Outerpack information

- Height [in]: 5.08
- Length [in]: 3.74
- Width [in]: 1.89

Packed product information

- MOQ (for professionals): 10
- Pack Quantity: 1

Highlights

Stand out in traffic

Philips MotoVision creates a distinctive orange reflection in the headlight that helps motorcycles and scooters stand out from other road traffic. Riders can be seen clearly by other drivers with the noticeable orange glow in their headlight lens and see further down the road.

Advanced technology

The technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. The Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful bright light, and precise beam performance. You get high-end style.

Maximum safety

Philips MotoVision headlight bulbs are designed with state-of-the-art technology to resist vibrations of up to 10G (gravitational force).

Ready, steady, installed!

Designed to be easily installed, drivers with maintenance experience will be able to upgrade compatible lights with ease.

Excellent Light Distribution

The bright output and intense color adds more than just style. They provide superior light distribution on the road so you can see and be seen better.

Reliable bright light

MotoVision is a great option for off-road by offering great vibration resistance on the road, and for off-road terrain. It is compatible with ATV's, snowmobiles and other powersports.

