

# PHILIPS

car headlight bulb

Vision

Type of lamp: HB3

Pack of: 1

12 V,65 W



9005PRB1



## Feel safe, drive safe

Up to 30% more vision compared to a standard lamp

Producing 30% more light compared to a standard car bulb, Vision headlight bulbs ensure excellent light-beam performance at a very competitive price with Original Equipment Quality for greater safety and comfort.

### **A better performance than a standard halogen bulb**

- Vision bulbs project 30% more light than standard halogens

### **Original equipment quality**

- Road safety begins with seeing and being seen
- Change both your headlamps at once for more safety

### **High quality upgrade headlight**

- Philips is the choice of major car manufacturers

# Highlights

## 30% More light on the road

Our lighting solutions produce a powerful and precise beam of light with maximum output. The Vision bulbs produce a longer beam for greater safety and comfort. We consistently produce the best, most efficient lighting solutions because we know that our high-quality lighting may one day save a life.

## Better visibility

Light is a fundamental part of the driving experience and light is the first and only part of the safety circle that actually helps to prevent accidents. Philips promotes active safety protection to prevent accidents by increasing overall visibility and road illumination.

## Car manufacturers' choice



For 100 years, Philips has been at the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

## Replace in pairs

It is highly recommended to replace your headlight bulbs in pairs for symmetric light performance.

# Specifications

## Packaging Data

EAN3: 8711500247254

EAN1: 8711500247247

## Packed product information

Pack Quantity: 1

MOQ (for professionals): 10

## Electrical characteristics

Voltage: 12 V

Wattage: 65 W

## Lifetime

Life time: 330h

Life time: 400+ hrs

## Product description

Technology: Halogen

Application: Dual beam

Base: P20d

DOT Compliant

Range: Vision

Type: HB3

## Marketing specifications

Product highlight: Up to 30% more vision

Expected benefits: More light

Product highlight: 30% More light

## Light characteristics

Color temperature: Up to 3200 K

