

# PHILIPS

Preliminary

car headlight bulb

CrystalVision

HB4

12.8V

55W

2x T10 LED lamps included

9006CVSL



## Drive with style

### Bright white light

Philips CrystalVision halogen headlamp upgrades the style of your car with 4300K bright white light. With the blue coating and the silver top finishing, your car will look more stylish

#### **Bright white light up to 4300K**


- CrystalVision 4300K bright white light for style upgrade
- Bright white color match effect for high end look

#### **High quality and ultra resistant headlamp**

- Philips car lamps are made of high-quality quartz glass<sup>^</sup>
- Philips car lamps are highly resistant against humidity<sup>^</sup>
- Philips car lamps are highly UV resistant
- Change both your headlamps simultaneously for more safety
- Philips is the choice of major car manufacturers.

# Highlights

## 4300K bright white light



With the blue coating and silver top design, CrystalVision is offering bright white headlight of 4300K to see and to be seen, for both city and country driving

## High-end look car

Supplied with two colour matching T10 LED position lamps, CrystalVision gives your car lights the premium look of high end cars.

## High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, eliminating the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability to withhold increased pressure inside the lamp, UV-quartz glass is able to produce more powerful lighting. ^Application varies per bulb type.

## Resistance against humidity

Only a burning bulb made of quartz glass (filament 2650°C, glass 800°C) can resist thermal shocks : such as, if a drop of cold water

touches the hot bulb, when you drive through water with a broken headlight unit.

^Application varies per bulb type

## UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensures their longevity

## Change by pairs



Highly recommended to change them by pairs for symmetric light performance

## Car manufacturers' choice

For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standards on modern automobiles. Today, one in two cars in Europe and one in three worldwide, is equipped with Philips lighting.

# Specifications

## Product description

**Technology:** Halogen  
**Application:** Additional high beam, High beam, Low beam  
**Designation:** HB4 CrystalVision  
**Homologation ECE:** NO  
**Range:** CrystalVision  
**Type:** HB4  
**Base:** P22d

## Electrical characteristics

**Voltage:** 12,8 V  
**Wattage:** 55 W

## Lifetime

**Life time:** B3/Tc(14V) = 180/360

## Light characteristics

**Color temperature:** up to 4300 K  
**Lumens [lm]:** 1095 ±15%

## Packaging Data

**EAN1:** 8727900354522  
**EAN3:** 8727900354539  
**Packaging type:** SL

## Ordering information

**Order entry:** 9006CVSL  
**Ordering code:** 35452230

## Marketing specifications

**Expected benefits:** Bright white light  
**Product highlight:** 4300K

## Outerpack information

**Gross weight per piece:** 2.53 kg  
**Height:** 12.6 cm  
**Length:** 27.6 cm  
**Width:** 22.8 cm

## Packed product information

**Gross weight per piece:** 126.5 g  
**Height:** 10.9 cm  
**Length:** 10.9 cm  
**Net weight per piece:** 20.4 g  
**Pack Quantity / MOQ:** 20  
**Width:** 5.3 cm

