

# PHILIPS

car headlight bulb

X-tremeVision G-force

Type of lamp: HB4

Pack of: 1

12V, 51W

More light

9006XVGB1



## Enjoy performance taken to new extremes

### Up to 130% brighter light

Philips X-tremeVision G-force HB4 car bulbs are among the brightest you can buy. They outshine most other car lamps with up to 130% more brightness and superior beam length. See further, react faster and drive safer.

#### Up to 130% brighter light for better visibility

- See further and react faster with up to 130% more brightness
- One of the brightest bulbs: ultimate light performance

#### White light for more contrast

- Significantly whiter light to improve comfort and safety

#### Durable lights

- A lifetime of safety so you can see and be seen

#### Enhanced safety

- Performance means more light and longer lifetime

#### Philips quality

- Philips is the choice of major car manufacturers

# Highlights

## Up to 130% more brightness

Perfect illumination is especially important in the distance – usually between 75-100 metres in front of your vehicle. Philips X-tremeVision G-force boosts your visibility with up to 130% more brightness. This helps you recognise obstacles and any potential dangers earlier than with most other halogen headlight lamps.

## Ultimate light performance

With its optimised high-precision filament geometry, up to 13 bar high-pressure gas filling, high-precision coating and high-quality UV-Quartz glass, Philips X-tremeVision G-force headlights confirm a milestone in automotive lighting. They are engineered for the ultimate performance and uncompromising visibility.

## Significantly whiter light

The bright white light of up to 3350 Kelvin is significantly whiter than standard headlamps. The Philips patented gradient coating technology produces a more powerful light. So you can enjoy one of the brightest lighting performances and a highly comfortable night driving experience.

## A lifetime of safety

Every potential failure of a spare part is a risk for you and your vehicle. This is especially true for headlights. Every broken headlight

lamp reduces visibility and safety for you and the oncoming traffic. Philips X-tremeVision G-force is optimised for a long and reliable lifetime. You can see and be seen for longer than with any other high-performance lamp.

## More light and higher lifetime

Philips X-tremeVision G-force headlights are made for outstanding performance, producing up to 130% brighter light, without compromising on the lifetime. With up to 450 hours\*, Philips X-tremeVision G-force's lifetime is significantly higher than competitor solutions in the more light category. (\*tested at 13.2V standard voltage).

## Highest quality car lighting

Technologically advanced Philips brand is renowned in the automotive industry, and has been for over 100 years. The Philips Original Equipment Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. X-tremeVision G-force is compatible with car models of major brands, such as Audi, BMW, Ford, GM, Toyota and Volkswagen. See the product selector guide for more information.

# Specifications

## Packaging Data

**Packaging type:** Blister  
**EAN1:** 8719018001948  
**EAN3:** 8719018001955

## Electrical characteristics

**Voltage:** 12 V  
**Wattage:** 51 W

## Lifetime

**Life time:** 600 hrs

## Light characteristics

**Lumens:** 1095 ±15%  
**Color temperature:** 3350 K

## Ordering information

**Order entry:** 9006XVGB1  
**Ordering code:** 194830

## Outerpack information

**Height:** 13 cm  
**Length:** 25.5 cm  
**Width:** 19 cm  
**Gross weight per piece:** 0.35 kg

## Product description

**Type:** HB4  
**Application:** High beam, Low beam  
**Homologation ECE**  
**Range:** X-tremeVision G-force  
**Technology:** Halogen  
**Designation:** 9006XVGB1  
**Base:** P22d

## Packed product information

**Height:** 13.3 cm  
**Length:** 9.5 cm  
**Width:** 5.3 cm  
**MOQ (for professionals):** 10  
**Pack Quantity:** 1  
**Gross weight per piece [g]:** 22.7

## Marketing specifications

**Expected benefits:** More light  
**Product highlight:** More light

