



Philips Standard
Conventional Interior and
Signaling

Type of lamp: HB5

Pack of: 1
12 V,65/55 W

9007C1



Feel safe, drive safe

Philips standard lamps

Our headlight lamps are the choice of all major car manufacturers. They offer best in class quality at a competitive price.

Original equipment manufacturer

- Philips is the choice of major car manufacturers

Wide range of 12V lamps

- Wide range of 12V lamps to meet all applications

Quality standards according to ECE regulations

- Respecting high quality standards of the ECE homologation

Change in pairs

- Change both your headlamps at once for more safety

PHILIPS

Conventional Interior and Signaling
Type of lamp: HB5 Pack of: 1, 12 V,65/55 W

Specifications

Electrical characteristics

- Voltage: 12 V
- Wattage: 65/55 W

Packaging Data

- EAN1: 8711500245502
- EAN3: 8727900370966
- Packaging type: C1

Product description

- Application: Daytime running light, Front fog
- Homologation ECE
- Range: Standard
- Technology: Halogen
- Type: HB5
- Designation: 9007C1
- Base: PX29t

Outerpack information

- Gross weight per piece: 0.539 kg

- Height: 9.9 cm
- Length: 27.5 cm
- Width: 11.4 cm

Packed product information

- Gross weight per piece: 47.1 g
- Height: 9.3 cm
- Length: 5.4 cm
- MOQ (for professionals): 10
- Net weight per piece: 40.1 g
- Pack Quantity: 1
- Width: 5.4 cm

Ordering information

- Order entry: 9007C1
- Ordering code: 24550230

Marketing specifications

- Expected benefits: Standard
- Product highlight: Philips standard lamps

9007C1

Highlights

Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

ECE homologation

We are dedicated to producing best-in-class Philips automotive products and services in the aftermarket. Our products are manufactured from high-quality materials and tested to the highest specifications to maximize the safety and driving comfort of our customers. Our entire production is meticulously tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000).

Designed for multiple usage

Which 12V lamp for which application? Philips Automotive offering includes all car specific functions : license plate lights, rear position/parking light, glove box lights, interior signaling, front parking lights.

Change in pairs

It is highly recommended to change them in pairs for symmetrical light performance.



Issue date 2017-07-25

Version: 3.0.1

12 NC: 8670 001 40863

© 2017 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com