



Philips X-tremeVision G-force
car headlight bulb

Type of lamp: HIR2

Pack of: 2
12V, 55 W
More light

9012XVGS2



Enjoy performance taken to new extremes

Up to 130% brighter light

Philips X-tremeVision G-force car bulbs are among the brightest you can buy. They outshine most other car lamps with up to 130% more brightness, superior beam length and 10G vibration resistance. See further, react faster and drive safer.

Up to 130% brighter light for better visibility

- See further and react faster with up to 130% more brightness
- One of the brightest bulbs: ultimate light performance

White light for more contrast

- Significantly whiter light to improve comfort and safety

Durable lights with up to 10G vibration resistance

- A lifetime of safety so you can see and be seen
- Performance means more light and longer lifetime
- Endurance performance bulbs for 10G* vibration resistance

Enhanced safety

- Among the safest road-legal headlights

Philips quality

- Philips is the choice of major car manufacturers

PHILIPS

car headlight bulb

Type of lamp: HIR2 Pack of: 2, 12V, 55 W, More light

Specifications

Packaging Data

- Packaging type: S2A
- EAN1: 8719018002105
- EAN3: 8719018002112

Electrical characteristics

- Voltage: 12 V
- Wattage: 55 W

Lifetime

- Life time: 300 hrs

Light characteristics

- Lumens: 1875 ±15%
- Color temperature: 3350 K

Ordering information

- Order entry: 9012XVGS2
- Ordering code: 210530

Outerpack information

- Height: 12 cm
- Length: 28.6 cm

- Width: 14.1 cm
- Gross weight per piece: 0.35 kg

Product description

- Type: HIR2
- Application: High beam, Low beam
- Homologation ECE
- Range: X-tremeVision G-force
- Technology: Halogen
- Base: PX22d
- Designation: 9012XVGS2

Packed product information

- Height: 13.3 cm
- Length: 11 cm
- Width: 5.3 cm
- MOQ (for professionals): 10
- Pack Quantity: 2
- Gross weight per piece [g]: 72.2

Marketing specifications

- Expected benefits: Performance
- Product highlight: More light

9012XVGS2

Highlights

Up to 130% more brightness

Perfect illumination is especially important in the distance – usually between 75-100 metres in front of your vehicle. Philips X-tremeVision G-force boosts your visibility with up to 130% more brightness. This helps you recognise obstacles and any potential dangers earlier than with most other halogen headlight lamps.

Ultimate light performance

With its optimised high-precision filament geometry, up to 13 bar high-pressure gas filling, high-precision coating and high-quality UV-Quartz glass, Philips X-tremeVision G-force headlights confirm a milestone in automotive lighting. They are engineered for the ultimate performance and uncompromising visibility.

Significantly whiter light

The bright white light of up to 3450 Kelvin is significantly whiter than standard headlamps. The Philips patented gradient coating technology produces a more powerful light. So you can enjoy one of the brightest lighting performances and a highly comfortable night driving experience.

A lifetime of safety

Every potential failure of a spare part is a risk for you and your vehicle. This is especially true for headlights. Every broken headlight lamp reduces visibility and safety for you and the oncoming traffic. Philips X-tremeVision G-force featuring precious xenon gas is optimised for a long and reliable lifetime. You can see and be seen for longer than with any other high-performance lamp.

More light and higher lifetime

Philips X-tremeVision G-force headlights are made for outstanding performance, producing up to 130% brighter light, without compromising on the lifetime. With up to 450 hours*, Philips X-tremeVision G-force's lifetime is significantly higher than competitor solutions in the more light category. (* H4 ,H7,HB3,HB4, tested at 13.2V standard voltage).

Vibration resistant endurance

"Don't let a pothole be the end of your car lights. Today's journeys can be a challenge to your car. Philips X-tremeVision G-force is designed to last. Tested for up to 10G* vibration resistance, these lamps underline their great endurance. (* 10 G vibration resistance, according IEC 60810, applies to H4, H7, H11, HIR2) "

Safe road-legal headlights

Philips X-tremeVision G-force is among the safest, easiest and most efficient way to upgrade your car headlights within legal parameters. The lights are fully ECE certified.

Highest quality car lighting

Technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. The Philips Original Equipment Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. X-tremeVision G-force is compatible with car models of major brands, such as Audi, BMW, Ford, GM, Toyota and Volkswagen. See the product selector guide for more information.



Issue date 2019-12-12

Version: 1.0.1

12 NC: 8670 001 63543

© 2019 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com