



Philips Ultinon LED
Car signaling bulb

921WLED-WHITE

Number of bulbs: 2
12 V, 6000 K daylight effect
Experience more light



921ULWX2

Bright signaling. Stylish driving.

Durable LED quality

For a stylish drive, benefit from signaling lights with intense colors. Philips Ultinon LED for reverse signaling are bright and look good so you can back-up in safety and with style.

Stylish look

- Brighter signaling for improved safety
- Upgrade your lights, upgrade your style

Brighter LED exterior lights

- 6000K daylight effect improves visibility when reversing

Long lasting LED lights

- Instant-on Performance
- Good light distribution for enhanced visibility

Good light diffusion

- Philips automotive lighting at the highest quality level

Durable Philips quality

- Easy installation and compatible with many car models
- Durable and long-lasting LED lighting

PHILIPS

Car signaling bulb

921WLED-WHITE Number of bulbs: 2, 12 V, 6000 K daylight effect, Experience more light

Highlights

Stylish exterior light

While the main goal of exterior lighting is to help you see and be seen, there's no reason why you shouldn't look good at the same time. If you're looking to upgrade your style, without buying a newer car, replacing your exterior lighting with LEDs is a smart way to spend your money. Upgrade your exterior lighting with a more intense red for stop lights, a vibrant amber for turning signals and bright white light for positioning and reversing. Your car is an expression of who you are, so make a style statement with Philips exterior signaling LED lights.

Be seen with bright signaling

Signaling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. Bright signaling lights ensures you are seen for improved safety. Whether it's reversing, turning, or stopping, Philips Ultinon LED signaling lights provide you with the performance you need, giving other drivers vital extra time to react to your movements.

See better when reversing

When reversing a car your vision is limited. Due to your seated position, you can't see all angles at once. And reversing in the dark is even more treacherous. So it's no surprise accidents are common when in reverse gear. Philips LED reverse lights provide a powerful daylight effect and up to 6000K, better illuminating the area immediately behind your car. And the more you can see, the safer you will be.

Good light diffusion

Philips LED exterior lighting range is designed for a smarter light distribution to ensure that exterior signaling light is projected where you need it

(whether that's reversing, stopping, or signaling).

With wide angle and good light diffusion, not only can you see more of the road, other drivers can see more of you.

Automotive grade quality

The technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. The Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful bright light, and precise beam performance. You get high-end style.

Ready, steady, installed!

Designed to be easily installed in compatible vehicles, drivers with maintenance experience will be able to upgrade compatible lights with ease.

Long-lasting LED lighting

You want bright and stylish car lights. But you don't want to keep replacing failed lamps. That is a major weakness of conventional lights: the more powerful the light, the shorter its lifespan. At the same light intensity, LEDs last longer. And Philips Ultinon LED lights have additional resistance to heat and vibration, making them a perfect choice for long-lasting performance, with a lifetime of up to 8 years.

Excellent Light Distribution

The bright output and intense color adds more than just style. They provide superior light distribution, with a wide angle beam on the road so you can see and be seen better.

921ULWX2

Specifications

Packaging Data

- EAN1: 46678721304
- EAN3: 50046678721309
- Packaging type: X2

Product description

- Technology: LED
- Application: Reverse
- Range: Ultinon LED
- Type: T16
- Homologation ECE: NO
- Base: W2.1X9.5D
- Designation LED Type: 921WLED-WHITE

Electrical characteristics

- Voltage: 12 V

Marketing specifications

- Expected benefits: Experience more light
- Product highlight: Bright signaling, Stylish Drive

Light characteristics

- Color temperature: Up to 6000K
- Lumens [lm]: 115

Ordering information

- Order entry: 921ULWX2
- Ordering code: 78721309

Outerpack information

- Gross weight per piece [lbs]: 0.82
- Height [in]: 3.54
- Length [in]: 7.87
- Width [in]: 5.91

Packed product information

- MOQ (for professionals): 10
- Pack Quantity: 2
- Gross weight per piece [lbs]: 0.01
- Height [in]: 3.54
- Length [in]: 2.76
- Width [in]: 1.18

Lifetime

- Life time: Up to 8 years



Issue date 2019-08-25

Version: 3.1.1

12 NC: 8670 001 50162

© 2019 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

* It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.