



Philips Standard
car headlight bulb

H7
55W
12V

923495717101

Original Equipment Quality

Original Equipment Quality

The Standard lamp is used by all manufacturers and you can find it in most brand new cars. Ensures efficiency, quality and excellent value for money.

Very high quality and ultra resistant car lamp

- Change both your headlamps simultaneously for more safety
- Philips is the choice of all major car manufacturers.

Original Equipment manufacturer

- Award winning car lamp manufacturer
- Respecting high quality standards of the ECE homologation
- Philips car lamps are highly resistant against humidity*
- Philips car lamps are highly UV resistant
- Philips car lamps are made of high-quality quartz glass

PHILIPS

Car headlight bulb
H7 55W, 12V

923495717101

Highlights

Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

Change by pairs




Highly recommended to change them by pairs for symmetric light performance

ECE homologation

Philips Automotive is dedicated to producing best-in-class products and services in the

Original Equipment Manufacturer market as well as in aftermarket. Our products are manufactured from high-quality materials and tested to the highest specifications to maximize the safety and driving comfort of our customers. Our entire production is meticulously tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements

Resistance against humidity



Only a burning bulb made of quartz glass (filament 2650°C, glass 800°C) can resist thermal shocks : such as, if a drop of cold water touches the hot bulb, when you drive through water with a broken headlight unit.

Rewarded Car lamps



Our lamps are often rewarded by automotive experts

UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass ideal for all driving conditions and ensures their longevity at the same time.

High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2650°C and glass 800°C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light

Car headlight bulb
H7 55W, 12V

923495717101

Specifications

Packaging Data

- EAN1: 8711500879875
- EAN3: 8711500879882
- Packaging type: C1

Product description

- Technology: Halogen
- Application: High beam, Low beam, fog beam
- Base: PX26d
- Designation: H7-12972-CI
- Range: Standard
- Type: H7
- Homologation ECE
- Marking ECE: E1 22Z

Marketing specifications

- Expected benefits: Long Life
- Product highlight: Original Equipment Quality

Ordering information

- Order entry: 12972C1
- Ordering code: 87987560

Outerpack information

- Gross weight per piece: 2980 g
- Height: 14.7 cm
- Length: 37.6 cm
- Net weight per piece: 1200 g
- Width: 18.6 cm

Packed product information

- Gross weight per piece: 5 g
- Height: 6.5 cm
- Length: 3.5 cm
- Net weight per piece: 0 g
- Width: 3.5 cm
- Pack Quantity / MOQ: 1

Electrical characteristics

- Voltage: 12 V
- Wattage: 55 W

Light characteristics

- Color temperature: 3200 K



Issue date 2015-05-07

Version: 1.0.1

12 NC: 8670 001 30136

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com